

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211979

Luminaire Tested: **LSR4B30D010BZ EC4B30509030 4LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211979
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30509030 4LBSGPH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2245.7 lumens
Efficiency: N/A
Efficacy: 80.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211979

CATALOG NUMBER: LSR4B30D010BZ EC4B30509030 4LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P211979

CATALOG NUMBER: LSR4B30D010BZ EC4B30509030 4LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			76
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66			66
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			57
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50			50
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45			45
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40			40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36			36
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32			32
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30			30

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211979

CATALOG NUMBER: LSR4B30D010BZ EC4B30509030 4LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.2	4.4
10°-20°	275.6	12.3
20°-30°	402.0	17.9
30°-40°	458.5	20.4
40°-50°	439.8	19.6
50°-60°	336.8	15.0
60°-70°	184.8	8.2
70°-80°	49.2	2.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	775.9	34.5
0°-40°	1234.3	55.0
0°-60°	2010.9	89.5
0°-90°	2245.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2245.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1043	
5°	1035	98
15°	978	276
25°	873	402
35°	733	458
45°	571	440
55°	377	337
65°	186	185
75°	43	49
85°	0	1
90°	0	



TEST NUMBER: P211979

CATALOG NUMBER: LSR4B30D010BZ EC4B30509030 4LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1043.0
2.5°	1040.3
5°	1034.9
7.5°	1026.8
10°	1016.0
12.5°	997.2
15°	978.3
17.5°	956.7
20°	932.5
22.5°	902.8
25°	873.2
27.5°	843.6
30°	805.8
32.5°	770.8
35°	733.1
37.5°	695.3
40°	657.6
42.5°	617.2
45°	571.4
47.5°	525.5
50°	477.0
52.5°	425.8
55°	377.3
57.5°	328.8
60°	277.6
62.5°	229.1
65°	186.0
67.5°	142.8
70°	105.1
72.5°	70.1
75°	43.1
77.5°	18.9
80°	5.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)