

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P430044

Luminaire Tested: **LAM4B112R709040DE010x1MW**

Issue Date: 11/23/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P430044  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-14)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 11/23/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LAM4B112R709040DE010x1MW  
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 70 DEG TIR OPTIC  
Light Source: HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1257.6 lumens  
Efficiency: N/A  
Efficacy: 87.9 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P430044

CATALOG NUMBER: LAM4B112R709040DE010x1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P430044

CATALOG NUMBER: LAM4B112R709040DE010x1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92		
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84		
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76		
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70		
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64		
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	64	60	58		
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55	54		
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50		
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46		
10	66	55	49	45	65	55	49	44	54	48	44	53	48	44	52	48	44	43		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	456080
5°	447620
10°	452795
15°	465580
20°	466396
25°	423095
30°	378057
35°	332051
40°	244486
45°	136897
50°	67392
55°	37762
60°	22893
65°	15060
70°	11108
75°	9913
80°	7387
85°	7359



TEST NUMBER: P430044

CATALOG NUMBER: LAM4B112R709040DE010x1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.4	6.9
10°-20°	256.8	20.4
20°-30°	356.4	28.3
30°-40°	335.3	26.7
40°-50°	160.1	12.7
50°-60°	42.3	3.4
60°-70°	13.3	1.1
70°-80°	5.5	0.4
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	699.7	55.6
0°-40°	1035.0	82.3
0°-60°	1237.4	98.4
0°-90°	1257.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1257.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	924	
5°	904	86
15°	912	257
25°	777	356
35°	551	335
45°	196	160
55°	44	42
65°	13	13
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P430044

CATALOG NUMBER: LAM4B112R709040DE010x1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	924.4
2.5°	912.8
5°	903.8
7.5°	902.5
10°	903.8
12.5°	906.3
15°	911.5
17.5°	911.5
20°	888.3
22.5°	839.2
25°	777.2
27.5°	715.3
30°	663.6
32.5°	613.3
35°	551.3
37.5°	471.2
40°	379.6
42.5°	282.7
45°	196.2
47.5°	130.4
50°	87.8
52.5°	60.7
55°	43.9
57.5°	31.0
60°	23.2
62.5°	16.8
65°	12.9
67.5°	9.0
70°	7.7
72.5°	6.5
75°	5.2
77.5°	3.9
80°	2.6
82.5°	2.6
85°	1.3
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)