

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P430956

Luminaire Tested: **LAMR4B112R209040DE010x1MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P430956
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-3)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B112R209040DE010x1MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 20 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1299.0 lumens
Efficiency: N/A
Efficacy: 90.8 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.33
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P430956

CATALOG NUMBER: LAMR4B112R209040DE010x1MW

Luminous Intensity Polar Plot





TEST NUMBER: P430956

CATALOG NUMBER: LAMR4B112R209040DE010x1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 | | | | | | | | | | | | | | | | |
| 1 | 115 | 113 | 111 | 110 | 113 | 111 | 109 | 108 | 107 | 106 | 105 | 103 | 102 | 101 | 100 | 99 | 99 | 97 | | | 97 | | | | | | | | | | | | | | | | |
| 2 | 112 | 108 | 105 | 103 | 110 | 106 | 104 | 102 | 103 | 101 | 100 | 101 | 99 | 97 | 98 | 97 | 95 | | | 94 | | | | | | | | | | | | | | | | | |
| 3 | 108 | 104 | 100 | 98 | 107 | 103 | 99 | 97 | 100 | 98 | 95 | 98 | 96 | 94 | 96 | 94 | 93 | | | 91 | | | | | | | | | | | | | | | | | |
| 4 | 105 | 100 | 97 | 94 | 104 | 99 | 96 | 93 | 97 | 94 | 92 | 95 | 93 | 91 | 94 | 92 | 90 | | | 89 | | | | | | | | | | | | | | | | | |
| 5 | 103 | 97 | 93 | 90 | 101 | 96 | 93 | 90 | 95 | 92 | 89 | 93 | 91 | 89 | 92 | 90 | 88 | | | 87 | | | | | | | | | | | | | | | | | |
| 6 | 100 | 94 | 90 | 88 | 99 | 94 | 90 | 87 | 92 | 89 | 87 | 91 | 88 | 86 | 90 | 88 | 86 | | | 85 | | | | | | | | | | | | | | | | | |
| 7 | 98 | 92 | 88 | 85 | 97 | 91 | 88 | 85 | 90 | 87 | 85 | 89 | 86 | 84 | 88 | 86 | 84 | | | 83 | | | | | | | | | | | | | | | | | |
| 8 | 96 | 90 | 86 | 83 | 95 | 89 | 86 | 83 | 88 | 85 | 83 | 87 | 85 | 82 | 87 | 84 | 82 | | | 81 | | | | | | | | | | | | | | | | | |
| 9 | 94 | 88 | 84 | 81 | 93 | 87 | 84 | 81 | 86 | 83 | 81 | 86 | 83 | 81 | 85 | 82 | 81 | | | 80 | | | | | | | | | | | | | | | | | |
| 10 | 92 | 86 | 82 | 80 | 91 | 85 | 82 | 80 | 85 | 82 | 79 | 84 | 81 | 79 | 83 | 81 | 79 | | | 78 | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | 0° |
|-----|---------|
| 0° | 4486843 |
| 5° | 3792535 |
| 10° | 2227605 |
| 15° | 797589 |
| 20° | 263887 |
| 25° | 105066 |
| 30° | 50191 |
| 35° | 28670 |
| 40° | 20739 |
| 45° | 17444 |
| 50° | 20110 |
| 55° | 16429 |
| 60° | 8190 |
| 65° | 7005 |
| 70° | 8655 |
| 75° | 9150 |
| 80° | 6819 |
| 85° | 6793 |



TEST NUMBER: P430956

CATALOG NUMBER: LAMR4B112R209040DE010x1MW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 627.0 | 48.3 |
| 10°-20° | 489.0 | 37.6 |
| 20°-30° | 101.5 | 7.8 |
| 30°-40° | 32.0 | 2.5 |
| 40°-50° | 20.6 | 1.6 |
| 50°-60° | 16.5 | 1.3 |
| 60°-70° | 6.5 | 0.5 |
| 70°-80° | 4.9 | 0.4 |
| 80°-90° | 1.0 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1217.5 | 93.7 |
| 0°-40° | 1249.5 | 96.2 |
| 0°-60° | 1286.6 | 99.0 |
| 0°-90° | 1299.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1299.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 9094 | |
| 5° | 7658 | 627 |
| 15° | 1562 | 489 |
| 25° | 193 | 101 |
| 35° | 48 | 32 |
| 45° | 25 | 21 |
| 55° | 19 | 17 |
| 65° | 6 | 6 |
| 75° | 5 | 5 |
| 85° | 1 | 1 |
| 90° | 0 | |



TEST NUMBER: P430956

CATALOG NUMBER: LAMR4B112R209040DE010x1MW

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 9094.1 |
| 2.5° | 8760.6 |
| 5° | 7657.6 |
| 7.5° | 6135.4 |
| 10° | 4446.4 |
| 12.5° | 2805.1 |
| 15° | 1561.5 |
| 17.5° | 858.8 |
| 20° | 502.6 |
| 22.5° | 307.3 |
| 25° | 193.0 |
| 27.5° | 127.4 |
| 30° | 88.1 |
| 32.5° | 61.9 |
| 35° | 47.6 |
| 37.5° | 38.1 |
| 40° | 32.2 |
| 42.5° | 27.4 |
| 45° | 25.0 |
| 47.5° | 25.0 |
| 50° | 26.2 |
| 52.5° | 25.0 |
| 55° | 19.1 |
| 57.5° | 13.1 |
| 60° | 8.3 |
| 62.5° | 7.1 |
| 65° | 6.0 |
| 67.5° | 6.0 |
| 70° | 6.0 |
| 72.5° | 6.0 |
| 75° | 4.8 |
| 77.5° | 3.6 |
| 80° | 2.4 |
| 82.5° | 1.2 |
| 85° | 1.2 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)