

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431146

Luminaire Tested: **LAMR4B112R609040DE010x1MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P431146
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B112R609040DE010x1MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1222.3 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P431146

CATALOG NUMBER: LAMR4B112R609040DE010x1MB

Luminous Intensity Polar Plot





TEST NUMBER: P431146

CATALOG NUMBER: LAMR4B112R609040DE010x1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94																											
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																											
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82																											
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77																											
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72																											
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	69	67																											
7	84	75	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63																											
8	80	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	60	59																											
9	77	67	62	58	76	67	61	58	66	61	57	65	60	57	64	60	57	56																											
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	693100
5°	669845
10°	663612
15°	647163
20°	597237
25°	534857
30°	413834
35°	247909
40°	95257
45°	34817
50°	1382
55°	1032
60°	1184
65°	700
70°	866
75°	1144
80°	1705
85°	0



TEST NUMBER: P431146

CATALOG NUMBER: LAMR4B112R609040DE010x1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.4	10.5
10°-20°	352.5	28.8
20°-30°	439.7	36.0
30°-40°	256.1	21.0
40°-50°	42.8	3.5
50°-60°	1.1	0.1
60°-70°	0.8	0.1
70°-80°	0.6	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	920.6	75.3
0°-40°	1176.7	96.3
0°-60°	1220.6	99.9
0°-90°	1222.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1222.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1405	
5°	1352	128
15°	1267	352
25°	982	440
35°	412	256
45°	50	43
55°	1	1
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P431146

CATALOG NUMBER: LAMR4B112R609040DE010x1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1404.8
2.5°	1381.6
5°	1352.5
7.5°	1335.9
10°	1324.6
12.5°	1306.2
15°	1267.0
17.5°	1208.2
20°	1137.5
22.5°	1065.6
25°	982.5
27.5°	867.2
30°	726.4
32.5°	569.0
35°	411.6
37.5°	259.6
40°	147.9
42.5°	86.7
45°	49.9
47.5°	17.2
50°	1.8
52.5°	1.2
55°	1.2
57.5°	1.2
60°	1.2
62.5°	1.2
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)