

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212001

Luminaire Tested: **LSR4B30D010BZ EC4B30509730 4LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212001
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30509730 4LBNGPH1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1020.5 lumens
Efficiency: N/A
Efficacy: 36.4 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212001

CATALOG NUMBER: LSR4B30D010BZ EC4B30509730 4LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P212001

CATALOG NUMBER: LSR4B30D010BZ EC4B30509730 4LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87		
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81		
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76		
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70		
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62		
8	80	70	64	60	78	70	64	60	68	63	60	67	63	59	66	62	59	58		
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54		
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	52	51		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212001

CATALOG NUMBER: LSR4B30D010BZ EC4B30509730 4LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.3	10.9
10°-20°	278.9	27.3
20°-30°	339.9	33.3
30°-40°	224.3	22.0
40°-50°	51.6	5.1
50°-60°	9.9	1.0
60°-70°	3.7	0.4
70°-80°	1.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	730.1	71.5
0°-40°	954.3	93.5
0°-60°	1015.9	99.5
0°-90°	1020.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1020.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1224	
5°	1194	111
15°	999	279
25°	747	340
35°	358	224
45°	57	52
55°	10	10
65°	2	4
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P212001

CATALOG NUMBER: LSR4B30D010BZ EC4B30509730 4LBNGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1223.8
2.5°	1221.3
5°	1194.1
7.5°	1157.0
10°	1107.6
12.5°	1058.1
15°	998.8
17.5°	937.0
20°	872.7
22.5°	815.8
25°	746.6
27.5°	677.4
30°	588.4
32.5°	479.6
35°	358.5
37.5°	249.7
40°	160.7
42.5°	98.9
45°	56.9
47.5°	29.7
50°	17.3
52.5°	14.8
55°	9.9
57.5°	7.4
60°	7.4
62.5°	4.9
65°	2.5
67.5°	2.5
70°	2.5
72.5°	2.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)