

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212021

Luminaire Tested: **LSR4B30D010BZ EC4B30508035 4LBCSMMS1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212021  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B30D010BZ EC4B30508035 4LBCSMMS1  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2636.6 lumens  
Efficiency: N/A  
Efficacy: 94.2 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212021

CATALOG NUMBER: LSR4B30D010BZ EC4B30508035 4LBCSMMS1

### Luminous Intensity Polar Plot





TEST NUMBER: P212021

CATALOG NUMBER: LSR4B30D010BZ EC4B30508035 4LBCSMMS1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88	88	88	88
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76	76	76	76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65	65	65	65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57	57	57	57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50	50	50	50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44	44	44	44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40	40	40	40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36	36	36	36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32	32	32	32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29	29	29	29

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212021

CATALOG NUMBER: LSR4B30D010BZ EC4B30508035 4LBCSMMS1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	114.1	4.3
10°-20°	320.2	12.1
20°-30°	467.6	17.7
30°-40°	534.9	20.3
40°-50°	514.0	19.5
50°-60°	396.9	15.1
60°-70°	221.5	8.4
70°-80°	64.5	2.4
80°-90°	2.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	901.9	34.2
0°-40°	1436.8	54.5
0°-60°	2347.8	89.0
0°-90°	2636.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2636.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1211	
5°	1200	114
15°	1136	320
25°	1016	468
35°	856	535
45°	670	514
55°	445	397
65°	222	222
75°	56	64
85°	2	3
90°	0	



TEST NUMBER: P212021

CATALOG NUMBER: LSR4B30D010BZ EC4B30508035 4LBCSMMS1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1210.8
2.5°	1210.8
5°	1200.5
7.5°	1195.4
10°	1178.4
12.5°	1157.9
15°	1135.7
17.5°	1113.6
20°	1081.2
22.5°	1055.6
25°	1016.4
27.5°	977.1
30°	937.9
32.5°	898.7
35°	856.1
37.5°	813.4
40°	764.0
42.5°	719.6
45°	670.2
47.5°	613.9
50°	561.1
52.5°	503.1
55°	445.1
57.5°	385.4
60°	329.1
62.5°	272.9
65°	221.7
67.5°	173.9
70°	129.6
72.5°	90.4
75°	56.3
77.5°	29.0
80°	10.2
82.5°	3.4
85°	1.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)