

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212023

Luminaire Tested: **LSR4B30D010BZ EC4B30508035 4LBMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212023
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30508035 4LBMB1
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1231.2 lumens
Efficiency: N/A
Efficacy: 44.0 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212023

CATALOG NUMBER: LSR4B30D010BZ EC4B30508035 4LBMB1

Luminous Intensity Polar Plot





TEST NUMBER: P212023

CATALOG NUMBER: LSR4B30D010BZ EC4B30508035 4LBMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82			
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	77			
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	70	65	83	75	69	65	73	68	65	72	68	65	71	67	64	63			
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59			
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212023

CATALOG NUMBER: LSR4B30D010BZ EC4B30508035 4LBMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.7	11.3
10°-20°	347.2	28.2
20°-30°	419.9	34.1
30°-40°	267.8	21.8
40°-50°	55.9	4.5
50°-60°	0.7	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	906.8	73.6
0°-40°	1174.6	95.4
0°-60°	1231.2	100.0
0°-90°	1231.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1231.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1546	
5°	1498	140
15°	1240	347
25°	934	420
35°	428	268
45°	58	56
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P212023

CATALOG NUMBER: LSR4B30D010BZ EC4B30508035 4LBMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1545.6
2.5°	1528.6
5°	1498.0
7.5°	1453.9
10°	1389.3
12.5°	1311.2
15°	1239.9
17.5°	1168.5
20°	1090.4
22.5°	1015.7
25°	934.1
27.5°	825.4
30°	706.5
32.5°	567.3
35°	428.0
37.5°	298.9
40°	197.0
42.5°	115.5
45°	57.7
47.5°	23.8
50°	6.8
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)