

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212049

Luminaire Tested: **LSR4B30D010BZ EC4B30509035 4LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212049
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30509035 4LBCSMB1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2470.0 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212049

CATALOG NUMBER: LSR4B30D010BZ EC4B30509035 4LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P212049

CATALOG NUMBER: LSR4B30D010BZ EC4B30509035 4LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88						88													
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75						75													
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65						65													
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56						56													
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49						49													
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43						43													
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39						39													
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35						35													
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31						31													
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28						28													

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212049

CATALOG NUMBER: LSR4B30D010BZ EC4B30509035 4LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.7	4.0
10°-20°	281.0	11.4
20°-30°	422.5	17.1
30°-40°	501.3	20.3
40°-50°	496.1	20.1
50°-60°	389.6	15.8
60°-70°	218.5	8.8
70°-80°	61.4	2.5
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	802.2	32.5
0°-40°	1303.5	52.8
0°-60°	2189.2	88.6
0°-90°	2470.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2470.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1043	
5°	1041	99
15°	997	281
25°	917	422
35°	804	501
45°	646	496
55°	439	390
65°	218	218
75°	53	61
85°	0	1
90°	0	



TEST NUMBER: P212049

CATALOG NUMBER: LSR4B30D010BZ EC4B30509035 4LBCSMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1043.0
2.5°	1039.4
5°	1041.2
7.5°	1032.4
10°	1021.7
12.5°	1009.3
15°	996.9
17.5°	981.0
20°	959.7
22.5°	938.5
25°	917.3
27.5°	894.2
30°	864.1
32.5°	834.0
35°	803.9
37.5°	768.5
40°	727.8
42.5°	688.8
45°	646.3
47.5°	598.5
50°	548.9
52.5°	492.3
55°	439.1
57.5°	378.9
60°	322.3
62.5°	270.9
65°	217.8
67.5°	171.8
70°	127.5
72.5°	86.8
75°	53.1
77.5°	26.6
80°	7.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)