

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P429810

Luminaire Tested: **LAM4B112R209727DE010x1MW**

Issue Date: 11/23/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P429810  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-3)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 11/23/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LAM4B112R209727DE010x1MW  
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 20 DEG TIR OPTIC  
Light Source: HIGH LUMEN LED 97CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1080.2 lumens  
Efficiency: N/A  
Efficacy: 75.5 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.33  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P429810  
CATALOG NUMBER: LAM4B112R209727DE010x1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P429810

CATALOG NUMBER: LAM4B112R209727DE010x1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	97				97															
2	112	108	105	103	110	106	104	102	103	101	100	101	99	97	98	97	95				94																
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93				91																
4	105	100	97	94	104	99	96	93	97	94	92	95	93	91	94	92	90				89																
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88				87																
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86				85																
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84				83																
8	96	90	86	83	95	89	86	83	88	85	83	87	85	82	87	84	82				81																
9	94	88	84	81	93	87	84	81	86	83	81	86	83	81	85	82	81				80																
10	92	86	82	80	91	85	82	80	85	82	79	84	81	79	83	81	79				78																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3730936
5°	3153595
10°	1852313
15°	663253
20°	219468
25°	87374
30°	41759
35°	23851
40°	17196
45°	14513
50°	16733
55°	13591
60°	6809
65°	5837
70°	7213
75°	7625
80°	5683
85°	5661



TEST NUMBER: P429810

CATALOG NUMBER: LAM4B112R209727DE010x1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	521.4	48.3
10°-20°	406.6	37.6
20°-30°	84.4	7.8
30°-40°	26.6	2.5
40°-50°	17.1	1.6
50°-60°	13.7	1.3
60°-70°	5.4	0.5
70°-80°	4.1	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1012.4	93.7
0°-40°	1039.0	96.2
0°-60°	1069.8	99.0
0°-90°	1080.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1080.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7562	
5°	6368	521
15°	1298	407
25°	160	84
35°	40	27
45°	21	17
55°	16	14
65°	5	5
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P429810

CATALOG NUMBER: LAM4B112R209727DE010x1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7562.0
2.5°	7284.6
5°	6367.5
7.5°	5101.7
10°	3697.3
12.5°	2332.5
15°	1298.5
17.5°	714.1
20°	418.0
22.5°	255.5
25°	160.5
27.5°	106.0
30°	73.3
32.5°	51.5
35°	39.6
37.5°	31.7
40°	26.7
42.5°	22.8
45°	20.8
47.5°	20.8
50°	21.8
52.5°	20.8
55°	15.8
57.5°	10.9
60°	6.9
62.5°	5.9
65°	5.0
67.5°	5.0
70°	5.0
72.5°	5.0
75°	4.0
77.5°	3.0
80°	2.0
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)