

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212069

Luminaire Tested: **LSR4B30D010BZ EC4B30509035 4LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212069
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30509035 4LBSMW1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2589.1 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212069

CATALOG NUMBER: LSR4B30D010BZ EC4B30509035 4LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P212069

CATALOG NUMBER: LSR4B30D010BZ EC4B30509035 4LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																												
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																												
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																												
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																												
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																												
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																												
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																												
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																												
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																												
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																												

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212069

CATALOG NUMBER: LSR4B30D010BZ EC4B30509035 4LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.8	3.8
10°-20°	281.7	10.9
20°-30°	424.3	16.4
30°-40°	504.9	19.5
40°-50°	504.0	19.5
50°-60°	409.9	15.8
60°-70°	252.1	9.7
70°-80°	97.7	3.8
80°-90°	15.7	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	804.9	31.1
0°-40°	1309.8	50.6
0°-60°	2223.7	85.9
0°-90°	2589.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2589.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1043	
5°	1040	99
15°	1000	282
25°	924	424
35°	808	505
45°	655	504
55°	459	410
65°	253	252
75°	89	98
85°	12	16
90°	0	



TEST NUMBER: P212069

CATALOG NUMBER: LSR4B30D010BZ EC4B30509035 4LBSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1043.2
2.5°	1044.7
5°	1040.1
7.5°	1034.0
10°	1026.3
12.5°	1012.5
15°	1000.2
17.5°	981.8
20°	961.9
22.5°	943.5
25°	923.5
27.5°	895.9
30°	868.3
32.5°	842.2
35°	808.5
37.5°	771.6
40°	737.9
42.5°	696.5
45°	655.0
47.5°	610.6
50°	563.0
52.5°	513.9
55°	458.7
57.5°	405.0
60°	352.8
62.5°	302.2
65°	253.1
67.5°	207.1
70°	164.1
72.5°	124.3
75°	89.0
77.5°	58.3
80°	35.3
82.5°	21.5
85°	12.3
87.5°	6.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)