

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431034

Luminaire Tested: **LAMR4B112R359727DE010x1MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P431034
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2008-908-6)
Test Lab: INNOVATION CENTER (G2)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B112R359727DE010x1MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 35 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1066.9 lumens
Efficiency: N/A
Efficacy: 74.6 lumens/watt
Spacing Criteria (0/90/45): 0.57 / 0.57 / 0.51
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P431034

CATALOG NUMBER: LAMR4B112R359727DE010x1MW

Luminous Intensity Polar Plot





TEST NUMBER: P431034

CATALOG NUMBER: LAMR4B112R359727DE010x1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96	96	96	96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	91	91
3	106	101	97	94	104	100	96	93	97	94	92	95	92	90	93	91	89	87	87	87	87
4	102	96	92	89	101	95	91	88	93	90	87	91	88	86	90	87	85	84	84	84	84
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81	81	81	81
6	96	89	84	81	94	88	84	80	87	83	80	85	82	79	84	81	79	78	78	78	78
7	92	85	81	77	91	85	80	77	84	80	77	82	79	76	81	78	76	75	75	75	75
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72	72	72	72
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70	70	70	70
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68	68	68	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1526763
5°	1491538
10°	1372614
15°	992096
20°	490076
25°	179810
30°	81069
35°	44149
40°	27373
45°	18490
50°	13893
55°	11870
60°	10460
65°	9923
70°	9232
75°	8006
80°	9092
85°	6227



TEST NUMBER: P431034

CATALOG NUMBER: LAMR4B112R359727DE010x1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	279.8	26.2
10°-20°	511.4	47.9
20°-30°	178.1	16.7
30°-40°	49.4	4.6
40°-50°	21.4	2.0
50°-60°	12.4	1.2
60°-70°	8.4	0.8
70°-80°	4.6	0.4
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	969.3	90.9
0°-40°	1018.7	95.5
0°-60°	1052.6	98.7
0°-90°	1066.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1066.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3094	
5°	3012	280
15°	1942	511
25°	330	178
35°	73	49
45°	26	21
55°	14	12
65°	8	8
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P431034

CATALOG NUMBER: LAMR4B112R359727DE010x1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3094.5
1°	3083.9
2°	3067.9
3°	3052.0
4°	3033.9
5°	3011.6
6°	2984.0
7°	2950.1
8°	2898.0
9°	2831.1
10°	2739.8
11°	2623.0
12°	2481.7
13°	2316.1
14°	2134.5
15°	1942.3
16°	1737.3
17°	1531.3
18°	1324.2
19°	1124.6
20°	933.4
22.5°	556.5
25°	330.3
26°	275.0
27°	229.4
28°	194.3
29°	165.7
30°	142.3
32.5°	100.9
35°	73.3
37.5°	55.2
40°	42.5
42.5°	32.9
45°	26.5
47.5°	22.3
50°	18.1
52.5°	15.9
55°	13.8
57.5°	11.7
60°	10.6
62.5°	9.6
65°	8.5
67.5°	7.4



TEST NUMBER: P431034

CATALOG NUMBER: LAMR4B112R359727DE010x1MW

CANDELA DISTRIBUTION (continued):

	0°
75°	4.2
77.5°	3.2
80°	3.2
82.5°	2.1
85°	1.1
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°	6.4
72.5°	5.3



(END OF REPORT)