

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P429789

Luminaire Tested: **LAM4B112R159730DE010x1MW**

Issue Date: 11/23/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P429789  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-6)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 11/23/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LAM4B112R159730DE010x1MW  
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 15 DEG TIR OPTIC  
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1128.0 lumens  
Efficiency: N/A  
Efficacy: 78.9 lumens/watt  
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29  
Luminous Opening: Circular (Dia: 0.29' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P429789  
CATALOG NUMBER: LAM4B112R159730DE010x1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P429789

CATALOG NUMBER: LAM4B112R159730DE010x1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1   | 116 | 114 | 112 | 111 | 113 | 112 | 110 | 109 | 108 | 107 | 106 | 104 | 103 | 103 | 101 | 100 | 100 | 98  |
| 2   | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 104 | 105 | 103 | 102 | 102 | 101 | 100 | 100 | 99  | 98  | 96  |
| 3   | 110 | 106 | 103 | 101 | 108 | 105 | 102 | 100 | 103 | 100 | 98  | 100 | 99  | 97  | 98  | 97  | 96  | 94  |
| 4   | 108 | 103 | 100 | 97  | 106 | 102 | 99  | 97  | 100 | 98  | 96  | 98  | 96  | 95  | 97  | 95  | 94  | 93  |
| 5   | 105 | 101 | 97  | 95  | 104 | 100 | 97  | 94  | 98  | 96  | 94  | 97  | 95  | 93  | 95  | 94  | 92  | 91  |
| 6   | 103 | 98  | 95  | 92  | 102 | 98  | 94  | 92  | 96  | 94  | 92  | 95  | 93  | 91  | 94  | 92  | 91  | 90  |
| 7   | 101 | 96  | 93  | 90  | 100 | 96  | 92  | 90  | 95  | 92  | 90  | 94  | 91  | 89  | 93  | 91  | 89  | 88  |
| 8   | 99  | 94  | 91  | 89  | 99  | 94  | 91  | 89  | 93  | 90  | 88  | 92  | 90  | 88  | 91  | 89  | 88  | 87  |
| 9   | 98  | 92  | 89  | 87  | 97  | 92  | 89  | 87  | 91  | 89  | 87  | 91  | 88  | 87  | 90  | 88  | 86  | 86  |
| 10  | 96  | 91  | 88  | 86  | 95  | 91  | 88  | 86  | 90  | 87  | 85  | 89  | 87  | 85  | 89  | 87  | 85  | 84  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1613535 |
| 5°  | 1361756 |
| 10° | 625614  |
| 15° | 195074  |
| 20° | 79498   |
| 25° | 26077   |
| 30° | 8092    |
| 35° | 1711    |
| 40° | 421     |
| 45° | 0       |
| 50° | 0       |
| 55° | 0       |
| 60° | 0       |
| 65° | 0       |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |



TEST NUMBER: P429789

CATALOG NUMBER: LAM4B112R159730DE010x1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 649.8  | 57.6      |
| 10°-20°   | 387.3  | 34.3      |
| 20°-30°   | 82.1   | 7.3       |
| 30°-40°   | 8.6    | 0.8       |
| 40°-50°   | 0.3    | 0.0       |
| 50°-60°   | 0.0    | 0.0       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1119.1 | 99.2      |
| 0°-40°    | 1127.7 | 100.0     |
| 0°-60°    | 1128.0 | 100.0     |
| 0°-90°    | 1128.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1128.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 10016 |      |
| 5°  | 8420  | 650  |
| 15° | 1170  | 387  |
| 25° | 147   | 82   |
| 35° | 9     | 9    |
| 45° | 0     | 0    |
| 55° | 0     | 0    |
| 65° | 0     | 0    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |



TEST NUMBER: P429789

CATALOG NUMBER: LAM4B112R159730DE010x1MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      |
|-------|---------|
| 0°    | 10015.5 |
| 2.5°  | 9699.1  |
| 5°    | 8420.5  |
| 7.5°  | 6233.6  |
| 10°   | 3824.3  |
| 12.5° | 2040.7  |
| 15°   | 1169.6  |
| 17.5° | 734.6   |
| 20°   | 463.7   |
| 22.5° | 273.5   |
| 25°   | 146.7   |
| 27.5° | 82.8    |
| 30°   | 43.5    |
| 32.5° | 22.0    |
| 35°   | 8.7     |
| 37.5° | 4.6     |
| 40°   | 2.0     |
| 42.5° | 0.5     |
| 45°   | 0.0     |
| 47.5° | 0.0     |
| 50°   | 0.0     |
| 52.5° | 0.0     |
| 55°   | 0.0     |
| 57.5° | 0.0     |
| 60°   | 0.0     |
| 62.5° | 0.0     |
| 65°   | 0.0     |
| 67.5° | 0.0     |
| 70°   | 0.0     |
| 72.5° | 0.0     |
| 75°   | 0.0     |
| 77.5° | 0.0     |
| 80°   | 0.0     |
| 82.5° | 0.0     |
| 85°   | 0.0     |
| 87.5° | 0.0     |
| 90°   | 0.0     |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)