

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212144

Luminaire Tested: **LSR4B30D010BZ EC4B30508050 4LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212144
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30508050 4LBMWH1
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2319.8 lumens
Efficiency: N/A
Efficacy: 82.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212144

CATALOG NUMBER: LSR4B30D010BZ EC4B30508050 4LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P212144

CATALOG NUMBER: LSR4B30D010BZ EC4B30508050 4LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	105	105	103	101	101	100	98	98	96	95	94																			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87																			
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81																			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76																			
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71																			
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	71	68	66																			
7	84	75	69	65	82	74	68	64	73	68	64	72	67	64	70	66	63	62																			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58																			
9	76	66	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55																			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212144

CATALOG NUMBER: LSR4B30D010BZ EC4B30508050 4LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	254.5	11.0
10°-20°	654.4	28.2
20°-30°	767.7	33.1
30°-40°	485.9	20.9
40°-50°	130.1	5.6
50°-60°	18.2	0.8
60°-70°	6.8	0.3
70°-80°	2.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1676.6	72.3
0°-40°	2162.5	93.2
0°-60°	2310.8	99.6
0°-90°	2319.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2319.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2755	
5°	2711	255
15°	2344	654
25°	1696	768
35°	771	486
45°	147	130
55°	17	18
65°	7	7
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P212144

CATALOG NUMBER: LSR4B30D010BZ EC4B30508050 4LBMWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2755.1
2.5°	2744.8
5°	2710.6
7.5°	2655.7
10°	2576.9
12.5°	2474.1
15°	2343.9
17.5°	2210.3
20°	2049.2
22.5°	1884.7
25°	1696.3
27.5°	1490.6
30°	1261.1
32.5°	1010.9
35°	771.0
37.5°	558.6
40°	383.8
42.5°	246.7
45°	147.4
47.5°	82.2
50°	44.5
52.5°	24.0
55°	17.1
57.5°	13.7
60°	10.3
62.5°	10.3
65°	6.9
67.5°	3.4
70°	3.4
72.5°	3.4
75°	3.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)