

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212150

Luminaire Tested: **LSR4B30D010BZ EC4B30508050 4LBNWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212150  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B30D010BZ EC4B30508050 4LBNWH1  
Description: PORTFOLIO 4 INCH CYLINDER  
NARROW DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1984.0 lumens  
Efficiency: N/A  
Efficacy: 70.9 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.62  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212150

CATALOG NUMBER: LSR4B30D010BZ EC4B30508050 4LBNWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P212150

CATALOG NUMBER: LSR4B30D010BZ EC4B30508050 4LBNWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95		
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89		
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84		
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79		
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75		
6	91	83	78	74	90	82	77	74	81	76	73	79	76	73	78	75	72	71		
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67		
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64		
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61		
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212150

CATALOG NUMBER: LSR4B30D010BZ EC4B30508050 4LBNWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	344.8	17.4
10°-20°	646.8	32.6
20°-30°	580.3	29.3
30°-40°	333.0	16.8
40°-50°	66.4	3.3
50°-60°	8.4	0.4
60°-70°	3.8	0.2
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1571.9	79.2
0°-40°	1904.9	96.0
0°-60°	1979.8	99.8
0°-90°	1984.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1984.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4216	
5°	3877	345
15°	2322	647
25°	1254	580
35°	528	333
45°	72	66
55°	10	8
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P212150

CATALOG NUMBER: LSR4B30D010BZ EC4B30508050 4LBNWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4216.5
2.5°	4130.9
5°	3877.4
7.5°	3507.5
10°	3103.3
12.5°	2705.9
15°	2322.3
17.5°	1986.6
20°	1698.9
22.5°	1459.2
25°	1253.6
27.5°	1089.2
30°	907.7
32.5°	722.7
35°	527.5
37.5°	359.7
40°	222.6
42.5°	133.6
45°	71.9
47.5°	30.8
50°	13.7
52.5°	10.3
55°	10.3
57.5°	6.9
60°	6.9
62.5°	3.4
65°	3.4
67.5°	3.4
70°	3.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)