

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431011

Luminaire Tested: **LAMR4B112R309730DE010x1MB**

Issue Date: 11/23/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P431011  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-8)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 11/23/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LAMR4B112R309730DE010x1MB  
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 30 DEG TIR OPTIC  
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1146.9 lumens  
Efficiency: N/A  
Efficacy: 80.2 lumens/watt  
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P431011

CATALOG NUMBER: LAMR4B112R309730DE010x1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P431011

CATALOG NUMBER: LAMR4B112R309730DE010x1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																																
RC	80									50									30									10									0																							
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																														
RCR																																																												
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																																	
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96	96	95	94	93	92	91	90	89	88	87	85	84	81																													
2	111	107	104	102	109	106	103	100	102	100	98	96	94	92	90	88	86	84	82	80	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50																									
3	107	103	99	96	105	101	98	95	99	96	94	92	90	88	86	84	82	80	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40																						
4	104	98	94	91	102	97	94	91	95	92	90	88	86	84	82	80	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36	34	32	30																			
5	101	95	90	87	99	94	90	87	92	89	86	84	82	80	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36	34	32	30	28	26	24	22	20																
6	98	91	87	84	97	91	87	84	89	86	83	81	79	77	75	73	71	69	67	65	63	61	59	57	55	53	51	49	47	45	43	41	39	37	35	33	31	29	27	25	23	21	19	17	15	13	11	9	7	5	3	1								
7	95	88	84	81	94	88	84	81	87	83	81	79	77	75	73	71	69	67	65	63	61	59	57	55	53	51	49	47	45	43	41	39	37	35	33	31	29	27	25	23	21	19	17	15	13	11	9	7	5	3	1									
8	92	86	81	79	91	85	81	78	84	81	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36	34	32	30	28	26	24	22	20	18	16	14	12	10	8	6	4	2	0										
9	90	83	79	76	89	83	79	76	82	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36	34	32	30	28	26	24	22	20	18	16	14	12	10	8	6	4	2	0											
10	88	81	77	74	87	80	76	74	80	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36	34	32	30	28	26	24	22	20	18	16	14	12	10	8	6	4	2	0												

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2077868
5°	2032465
10°	1762235
15°	1092261
20°	400346
25°	133810
30°	65687
35°	32765
40°	20288
45°	12908
50°	9211
55°	7484
60°	6414
65°	5137
70°	6347
75°	6291
80°	6251
85°	6227



TEST NUMBER: P431011

CATALOG NUMBER: LAMR4B112R309730DE010x1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	374.0	32.6
10°-20°	564.7	49.2
20°-30°	137.7	12.0
30°-40°	37.7	3.3
40°-50°	15.2	1.3
50°-60°	8.1	0.7
60°-70°	4.9	0.4
70°-80°	3.8	0.3
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1076.3	93.9
0°-40°	1114.0	97.1
0°-60°	1137.3	99.2
0°-90°	1146.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1146.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4212	
5°	4104	374
15°	2138	565
25°	246	138
35°	54	38
45°	18	15
55°	9	8
65°	4	5
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P431011

CATALOG NUMBER: LAMR4B112R309730DE010x1MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4211.5
2.5°	4183.2
5°	4103.8
7.5°	3914.5
10°	3517.5
12.5°	2895.4
15°	2138.4
17.5°	1378.1
20°	762.5
22.5°	406.8
25°	245.8
27.5°	166.4
30°	115.3
32.5°	78.3
35°	54.4
37.5°	40.2
40°	31.5
42.5°	23.9
45°	18.5
47.5°	15.2
50°	12.0
52.5°	10.9
55°	8.7
57.5°	7.6
60°	6.5
62.5°	5.4
65°	4.4
67.5°	4.4
70°	4.4
72.5°	4.4
75°	3.3
77.5°	3.3
80°	2.2
82.5°	1.1
85°	1.1
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)