

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P430128

Luminaire Tested: **LAM4B212R309024DE010x1MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P430128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B212R309024DE010x1MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 30 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2050.3 lumens
Efficiency: N/A
Efficacy: 72.2 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 28.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P430128

CATALOG NUMBER: LAM4B212R309024DE010x1MW

Luminous Intensity Polar Plot





TEST NUMBER: P430128

CATALOG NUMBER: LAM4B212R309024DE010x1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																										
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96	96	95	94	93	92	91	90	89	88	87	85	84	81																							
2	111	107	104	102	109	106	103	100	102	100	98	96	94	92	91	90	89	88	87	86	85	84	83	82	81	80	79	78	77	76	74																							
3	107	103	99	96	105	101	98	95	99	96	94	93	91	89	88	86	85	84	83	82	81	80	79	78	77	76	75	74	73	72																								
4	104	98	94	91	102	97	94	91	95	92	90	89	88	87	86	85	84	83	82	81	80	79	78	77	76	75	74	73	72																									
5	101	95	91	87	99	94	90	87	92	89	86	85	84	83	82	81	80	79	78	77	76	75	74	73	72																													
6	98	91	87	84	97	91	87	84	89	86	83	82	81	80	79	78	77	76	75	74	73	72																																
7	95	88	84	81	94	88	84	81	87	83	81	80	79	78	77	76	75	74	73	72																																		
8	92	86	81	79	91	85	81	78	84	81	78	77	76	75	74	73	72																																					
9	90	83	79	76	89	83	79	76	82	78	76	75	74	73	72																																							
10	88	81	77	74	87	80	77	74	80	76	74	73	72																																									

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3714852
5°	3633654
10°	3150580
15°	1952728
20°	715687
25°	239257
30°	117416
35°	58544
40°	36325
45°	23095
50°	16426
55°	13419
60°	11545
65°	9106
70°	11252
75°	11056
80°	11081
85°	10756



TEST NUMBER: P430128

CATALOG NUMBER: LAM4B212R309024DE010x1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	668.7	32.6
10°-20°	1009.5	49.2
20°-30°	246.1	12.0
30°-40°	67.4	3.3
40°-50°	27.1	1.3
50°-60°	14.5	0.7
60°-70°	8.7	0.4
70°-80°	6.7	0.3
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1924.3	93.9
0°-40°	1991.7	97.1
0°-60°	2033.4	99.2
0°-90°	2050.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2050.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7529	
5°	7337	669
15°	3823	1010
25°	440	246
35°	97	67
45°	33	27
55°	16	15
65°	8	9
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P430128

CATALOG NUMBER: LAM4B212R309024DE010x1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	7529.4
2.5°	7478.8
5°	7336.8
7.5°	6998.5
10°	6288.7
12.5°	5176.4
15°	3823.0
17.5°	2463.8
20°	1363.1
22.5°	727.3
25°	439.5
27.5°	297.5
30°	206.1
32.5°	140.0
35°	97.2
37.5°	71.9
40°	56.4
42.5°	42.8
45°	33.1
47.5°	27.2
50°	21.4
52.5°	19.4
55°	15.6
57.5°	13.6
60°	11.7
62.5°	9.7
65°	7.8
67.5°	7.8
70°	7.8
72.5°	7.8
75°	5.8
77.5°	5.8
80°	3.9
82.5°	1.9
85°	1.9
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)