

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P430248

Luminaire Tested: **LAM4B212R559024DE010x1MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P430248
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-898-142)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B212R559024DE010x1MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 55 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2032.3 lumens
Efficiency: N/A
Efficacy: 71.6 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.81
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 28.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P430248

CATALOG NUMBER: LAM4B212R559024DE010x1MW

Luminous Intensity Polar Plot





TEST NUMBER: P430248

CATALOG NUMBER: LAM4B212R559024DE010x1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 |
| 1 | 114 | 112 | 109 | 107 | 112 | 110 | 108 | 106 | 105 | 104 | 102 | 102 | 101 | 99 | 98 | 97 | 97 | 95 | | | 95 |
| 2 | 109 | 105 | 101 | 98 | 107 | 103 | 100 | 97 | 100 | 97 | 95 | 97 | 95 | 93 | 94 | 93 | 91 | 90 | | | 90 |
| 3 | 105 | 99 | 95 | 91 | 103 | 98 | 94 | 90 | 95 | 92 | 89 | 93 | 90 | 88 | 91 | 88 | 86 | 85 | | | 85 |
| 4 | 100 | 94 | 89 | 85 | 99 | 92 | 88 | 85 | 90 | 87 | 84 | 88 | 85 | 83 | 87 | 84 | 82 | 80 | | | 80 |
| 5 | 96 | 89 | 83 | 80 | 94 | 88 | 83 | 79 | 86 | 82 | 79 | 84 | 81 | 78 | 83 | 80 | 77 | 76 | | | 76 |
| 6 | 92 | 84 | 79 | 75 | 91 | 83 | 78 | 75 | 82 | 78 | 74 | 81 | 77 | 74 | 79 | 76 | 73 | 72 | | | 72 |
| 7 | 88 | 80 | 75 | 71 | 87 | 79 | 74 | 71 | 78 | 74 | 70 | 77 | 73 | 70 | 76 | 72 | 70 | 68 | | | 68 |
| 8 | 84 | 76 | 71 | 67 | 83 | 75 | 70 | 67 | 74 | 70 | 67 | 73 | 69 | 66 | 72 | 69 | 66 | 65 | | | 65 |
| 9 | 81 | 72 | 67 | 64 | 80 | 72 | 67 | 63 | 71 | 66 | 63 | 70 | 66 | 63 | 69 | 66 | 63 | 62 | | | 62 |
| 10 | 78 | 69 | 64 | 60 | 77 | 69 | 64 | 60 | 68 | 63 | 60 | 67 | 63 | 60 | 66 | 63 | 60 | 59 | | | 59 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 1367796 |
| 5° | 1386938 |
| 10° | 1419407 |
| 15° | 1360065 |
| 20° | 1235690 |
| 25° | 993065 |
| 30° | 571643 |
| 35° | 165935 |
| 40° | 25376 |
| 45° | 0 |
| 50° | 0 |
| 55° | 0 |
| 60° | 0 |
| 65° | 0 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P430248

CATALOG NUMBER: LAM4B212R559024DE010x1MW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 268.6 | 13.2 |
| 10°-20° | 740.8 | 36.5 |
| 20°-30° | 799.6 | 39.3 |
| 30°-40° | 218.7 | 10.8 |
| 40°-50° | 4.6 | 0.2 |
| 50°-60° | 0.0 | 0.0 |
| 60°-70° | 0.0 | 0.0 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1809.0 | 89.0 |
| 0°-40° | 2027.7 | 99.8 |
| 0°-60° | 2032.3 | 100.0 |
| 0°-90° | 2032.3 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2032.3 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2772 | |
| 5° | 2800 | 269 |
| 15° | 2663 | 741 |
| 25° | 1824 | 800 |
| 35° | 276 | 219 |
| 45° | 0 | 5 |
| 55° | 0 | 0 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P430248

CATALOG NUMBER: LAM4B212R559024DE010x1MW

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 2772.3 |
| 2.5° | 2761.1 |
| 5° | 2800.4 |
| 7.5° | 2831.4 |
| 10° | 2833.2 |
| 12.5° | 2761.1 |
| 15° | 2662.7 |
| 17.5° | 2532.5 |
| 20° | 2353.5 |
| 22.5° | 2123.0 |
| 25° | 1824.2 |
| 27.5° | 1442.8 |
| 30° | 1003.4 |
| 32.5° | 550.0 |
| 35° | 275.5 |
| 37.5° | 118.1 |
| 40° | 39.4 |
| 42.5° | 5.6 |
| 45° | 0.0 |
| 47.5° | 0.0 |
| 50° | 0.0 |
| 52.5° | 0.0 |
| 55° | 0.0 |
| 57.5° | 0.0 |
| 60° | 0.0 |
| 62.5° | 0.0 |
| 65° | 0.0 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)