

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212191

Luminaire Tested: **LSR4B30D010BZ EC4B30509050 4LBWLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212191  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B30D010BZ EC4B30509050 4LBWL1  
Description: PORTFOLIO 4 INCH CYLINDER  
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2518.3 lumens  
Efficiency: N/A  
Efficacy: 89.9 lumens/watt  
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212191

CATALOG NUMBER: LSR4B30D010BZ EC4B30509050 4LBWL11

### Luminous Intensity Polar Plot





TEST NUMBER: P212191

CATALOG NUMBER: LSR4B30D010BZ EC4B30509050 4LBWL11

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92																			
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84																			
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77																			
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70																			
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64																			
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58																			
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54																			
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49																			
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45																			
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212191

CATALOG NUMBER: LSR4B30D010BZ EC4B30509050 4LBWL11

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	150.9	6.0
10°-20°	476.2	18.9
20°-30°	742.8	29.5
30°-40°	722.8	28.7
40°-50°	361.0	14.3
50°-60°	55.9	2.2
60°-70°	6.8	0.3
70°-80°	1.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1369.9	54.4
0°-40°	2092.7	83.1
0°-60°	2509.6	99.7
0°-90°	2518.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2518.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1543	
5°	1563	151
15°	1681	476
25°	1632	743
35°	1174	723
45°	453	361
55°	46	56
65°	6	7
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P212191

CATALOG NUMBER: LSR4B30D010BZ EC4B30509050 4LBWLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1543.0
2.5°	1548.8
5°	1563.2
7.5°	1586.3
10°	1615.1
12.5°	1652.6
15°	1681.4
17.5°	1704.5
20°	1707.4
22.5°	1687.2
25°	1632.4
27.5°	1551.6
30°	1450.7
32.5°	1323.8
35°	1173.8
37.5°	1009.4
40°	836.4
42.5°	651.8
45°	452.8
47.5°	291.3
50°	175.9
52.5°	95.2
55°	46.1
57.5°	20.2
60°	11.5
62.5°	8.7
65°	5.8
67.5°	5.8
70°	2.9
72.5°	2.9
75°	2.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)