

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212195

Luminaire Tested: **LSR4B40D010BZ EC4B30509024 4LBCSMMS1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212195
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30509024 4LBCSMMS1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2604.1 lumens
Efficiency: N/A
Efficacy: 62.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212195

CATALOG NUMBER: LSR4B40D010BZ EC4B30509024 4LBCSMMS1

Luminous Intensity Polar Plot





TEST NUMBER: P212195

CATALOG NUMBER: LSR4B40D010BZ EC4B30509024 4LBCSMMS1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88																			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76																			
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65																			
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57																			
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50																			
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44																			
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40																			
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36																			
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32																			
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212195

CATALOG NUMBER: LSR4B40D010BZ EC4B30509024 4LBCSMMS1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.7	4.3
10°-20°	316.2	12.1
20°-30°	461.9	17.7
30°-40°	528.3	20.3
40°-50°	507.7	19.5
50°-60°	392.1	15.1
60°-70°	218.8	8.4
70°-80°	63.7	2.4
80°-90°	2.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	890.8	34.2
0°-40°	1419.1	54.5
0°-60°	2318.9	89.0
0°-90°	2604.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2604.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1196	
5°	1186	113
15°	1122	316
25°	1004	462
35°	846	528
45°	662	508
55°	440	392
65°	219	219
75°	56	64
85°	2	3
90°	0	



TEST NUMBER: P212195

CATALOG NUMBER: LSR4B40D010BZ EC4B30509024 4LBCSMMS1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1195.9
2.5°	1195.9
5°	1185.8
7.5°	1180.7
10°	1163.9
12.5°	1143.7
15°	1121.8
17.5°	1099.9
20°	1067.9
22.5°	1042.6
25°	1003.9
27.5°	965.1
30°	926.4
32.5°	887.6
35°	845.5
37.5°	803.4
40°	754.6
42.5°	710.8
45°	661.9
47.5°	606.4
50°	554.1
52.5°	496.9
55°	439.6
57.5°	380.7
60°	325.1
62.5°	269.5
65°	219.0
67.5°	171.8
70°	128.0
72.5°	89.3
75°	55.6
77.5°	28.6
80°	10.1
82.5°	3.4
85°	1.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)