

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212209

Luminaire Tested: **LSR4B40D010BZ EC4B30509024 4LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212209
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30509024 4LBPSMW1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3149.2 lumens
Efficiency: N/A
Efficacy: 75.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212209

CATALOG NUMBER: LSR4B40D010BZ EC4B30509024 4LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P212209

CATALOG NUMBER: LSR4B40D010BZ EC4B30509024 4LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																			
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212209

CATALOG NUMBER: LSR4B40D010BZ EC4B30509024 4LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.2	3.8
10°-20°	342.7	10.9
20°-30°	516.1	16.4
30°-40°	614.1	19.5
40°-50°	613.0	19.5
50°-60°	498.5	15.8
60°-70°	306.7	9.7
70°-80°	118.8	3.8
80°-90°	19.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	979.0	31.1
0°-40°	1593.1	50.6
0°-60°	2704.6	85.9
0°-90°	3149.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3149.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1269	
5°	1265	120
15°	1217	343
25°	1123	516
35°	983	614
45°	797	613
55°	558	499
65°	308	307
75°	108	119
85°	15	19
90°	0	



TEST NUMBER: P212209

CATALOG NUMBER: LSR4B40D010BZ EC4B30509024 4LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1268.8
2.5°	1270.7
5°	1265.1
7.5°	1257.6
10°	1248.3
12.5°	1231.5
15°	1216.6
17.5°	1194.2
20°	1169.9
22.5°	1147.5
25°	1123.3
27.5°	1089.7
30°	1056.1
32.5°	1024.4
35°	983.3
37.5°	938.6
40°	897.5
42.5°	847.1
45°	796.7
47.5°	742.6
50°	684.8
52.5°	625.1
55°	557.9
57.5°	492.6
60°	429.2
62.5°	367.6
65°	307.9
67.5°	251.9
70°	199.7
72.5°	151.1
75°	108.2
77.5°	70.9
80°	42.9
82.5°	26.1
85°	14.9
87.5°	7.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)