

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431399

Luminaire Tested: **LAMR4B212R559024DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P431399
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-898-142)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B212R559024DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 55 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2032.3 lumens
Efficiency: N/A
Efficacy: 71.6 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.81
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 28.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P431399

CATALOG NUMBER: LAMR4B212R559024DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P431399

CATALOG NUMBER: LAMR4B212R559024DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90			
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85			
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	80			
5	96	89	83	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76			
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72			
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	72	69	66	65			
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62			
10	78	69	64	60	77	69	64	60	68	63	60	67	63	60	66	63	60	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1367796
5°	1386938
10°	1419407
15°	1360065
20°	1235690
25°	993065
30°	571643
35°	165935
40°	25376
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P431399

CATALOG NUMBER: LAMR4B212R559024DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	268.6	13.2
10°-20°	740.8	36.5
20°-30°	799.6	39.3
30°-40°	218.7	10.8
40°-50°	4.6	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1809.0	89.0
0°-40°	2027.7	99.8
0°-60°	2032.3	100.0
0°-90°	2032.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2032.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2772	
5°	2800	269
15°	2663	741
25°	1824	800
35°	276	219
45°	0	5
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P431399

CATALOG NUMBER: LAMR4B212R559024DE010x1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2772.3
2.5°	2761.1
5°	2800.4
7.5°	2831.4
10°	2833.2
12.5°	2761.1
15°	2662.7
17.5°	2532.5
20°	2353.5
22.5°	2123.0
25°	1824.2
27.5°	1442.8
30°	1003.4
32.5°	550.0
35°	275.5
37.5°	118.1
40°	39.4
42.5°	5.6
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)