

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212237

Luminaire Tested: **LSR4B40D010BZ EC4B30508027 4LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212237
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30508027 4LBNWH1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2567.8 lumens
Efficiency: N/A
Efficacy: 61.4 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.62
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212237

CATALOG NUMBER: LSR4B40D010BZ EC4B30508027 4LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P212237

CATALOG NUMBER: LSR4B40D010BZ EC4B30508027 4LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95																																				
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89																																				
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84																																				
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79																																				
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75																																				
6	91	83	78	74	90	82	77	74	81	76	73	79	76	73	78	75	72	71																																				
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67																																				
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64																																				
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61																																				
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212237

CATALOG NUMBER: LSR4B40D010BZ EC4B30508027 4LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	446.2	17.4
10°-20°	837.1	32.6
20°-30°	751.1	29.3
30°-40°	431.0	16.8
40°-50°	86.0	3.3
50°-60°	10.9	0.4
60°-70°	4.9	0.2
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2034.5	79.2
0°-40°	2465.4	96.0
0°-60°	2562.3	99.8
0°-90°	2567.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2567.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5457	
5°	5018	446
15°	3006	837
25°	1622	751
35°	683	431
45°	93	86
55°	13	11
65°	4	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P212237

CATALOG NUMBER: LSR4B40D010BZ EC4B30508027 4LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	5457.2
2.5°	5346.4
5°	5018.3
7.5°	4539.5
10°	4016.4
12.5°	3502.2
15°	3005.7
17.5°	2571.2
20°	2198.8
22.5°	1888.5
25°	1622.5
27.5°	1409.7
30°	1174.8
32.5°	935.4
35°	682.7
37.5°	465.5
40°	288.2
42.5°	172.9
45°	93.1
47.5°	39.9
50°	17.7
52.5°	13.3
55°	13.3
57.5°	8.9
60°	8.9
62.5°	4.4
65°	4.4
67.5°	4.4
70°	4.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)