

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212240

Luminaire Tested: **LSR4B40D010BZ EC4B30508027 4LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212240
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30508027 4LBSGPH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3523.3 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212240

CATALOG NUMBER: LSR4B40D010BZ EC4B30508027 4LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P212240

CATALOG NUMBER: LSR4B40D010BZ EC4B30508027 4LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88			
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66			
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50			
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45			
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36			
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32			
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212240

CATALOG NUMBER: LSR4B40D010BZ EC4B30508027 4LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.1	4.4
10°-20°	432.5	12.3
20°-30°	630.8	17.9
30°-40°	719.3	20.4
40°-50°	690.0	19.6
50°-60°	528.5	15.0
60°-70°	290.0	8.2
70°-80°	77.1	2.2
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1217.3	34.6
0°-40°	1936.6	55.0
0°-60°	3155.0	89.5
0°-90°	3523.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3523.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1636	
5°	1624	154
15°	1535	432
25°	1370	631
35°	1150	719
45°	896	690
55°	592	528
65°	292	290
75°	68	77
85°	0	1
90°	0	



TEST NUMBER: P212240

CATALOG NUMBER: LSR4B40D010BZ EC4B30508027 4LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1636.3
2.5°	1632.1
5°	1623.7
7.5°	1611.0
10°	1594.1
12.5°	1564.5
15°	1534.9
17.5°	1501.0
20°	1463.0
22.5°	1416.5
25°	1370.0
27.5°	1323.5
30°	1264.3
32.5°	1209.3
35°	1150.1
37.5°	1090.9
40°	1031.7
42.5°	968.3
45°	896.4
47.5°	824.5
50°	748.4
52.5°	668.1
55°	592.0
57.5°	515.9
60°	435.5
62.5°	359.4
65°	291.8
67.5°	224.1
70°	164.9
72.5°	109.9
75°	67.7
77.5°	29.6
80°	8.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)