

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212265

Luminaire Tested: **LSR4B40D010BZ EC4B30509027 4LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212265
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30509027 4LBNMW1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2395.3 lumens
Efficiency: N/A
Efficacy: 57.3 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.95
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212265
CATALOG NUMBER: LSR4B40D010BZ EC4B30509027 4LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P212265

CATALOG NUMBER: LSR4B40D010BZ EC4B30509027 4LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	105	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	80	96	89	83	79	86	82	78	84	80	76	81	78	75	73		
4	92	83	76	71	90	82	76	71	80	74	70	78	73	69	76	72	68	67		
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61		
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56		
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	62	57	53	52		
8	73	62	55	50	71	61	55	50	60	54	50	59	53	49	58	53	49	48		
9	69	58	51	46	68	57	51	46	56	50	46	55	50	46	54	49	46	44		
10	65	54	48	43	64	54	47	43	53	47	43	52	47	43	51	46	43	41		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212265

CATALOG NUMBER: LSR4B40D010BZ EC4B30509027 4LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.0	7.8
10°-20°	491.8	20.5
20°-30°	647.4	27.0
30°-40°	503.9	21.0
40°-50°	244.7	10.2
50°-60°	154.6	6.5
60°-70°	99.7	4.2
70°-80°	52.2	2.2
80°-90°	12.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1327.2	55.4
0°-40°	1831.1	76.4
0°-60°	2230.5	93.1
0°-90°	2395.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2395.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2043	
5°	2005	188
15°	1754	492
25°	1427	647
35°	807	504
45°	304	245
55°	171	155
65°	99	100
75°	50	52
85°	11	13
90°	0	



TEST NUMBER: P212265

CATALOG NUMBER: LSR4B40D010BZ EC4B30509027 4LBNMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2043.4
2.5°	2032.0
5°	2005.3
7.5°	1959.7
10°	1898.8
12.5°	1830.3
15°	1754.2
17.5°	1674.3
20°	1590.6
22.5°	1510.7
25°	1426.9
27.5°	1320.4
30°	1175.8
32.5°	1004.6
35°	806.7
37.5°	624.0
40°	483.3
42.5°	376.7
45°	304.4
47.5°	247.3
50°	216.9
52.5°	194.1
55°	171.2
57.5°	152.2
60°	133.2
62.5°	114.2
65°	98.9
67.5°	87.5
70°	72.3
72.5°	60.9
75°	49.5
77.5°	38.1
80°	26.6
82.5°	19.0
85°	11.4
87.5°	3.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)