

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212303

Luminaire Tested: **LSR4B40D010BZ EC4B30509727 4LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212303
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30509727 4LBSWMH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2906.6 lumens
Efficiency: N/A
Efficacy: 69.5 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212303

CATALOG NUMBER: LSR4B40D010BZ EC4B30509727 4LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P212303

CATALOG NUMBER: LSR4B40D010BZ EC4B30509727 4LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90																			
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79																			
3	96	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70																			
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62																			
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56																			
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50																			
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45																			
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41																			
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38																			
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212303

CATALOG NUMBER: LSR4B40D010BZ EC4B30509727 4LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.3	5.9
10°-20°	451.2	15.5
20°-30°	606.0	20.8
30°-40°	620.3	21.3
40°-50°	536.9	18.5
50°-60°	357.1	12.3
60°-70°	146.7	5.0
70°-80°	17.4	0.6
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1227.4	42.2
0°-40°	1847.7	63.6
0°-60°	2741.8	94.3
0°-90°	2906.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2906.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1842	
5°	1814	170
15°	1612	451
25°	1322	606
35°	991	620
45°	699	537
55°	396	357
65°	145	147
75°	8	17
85°	0	1
90°	0	



TEST NUMBER: P212303

CATALOG NUMBER: LSR4B40D010BZ EC4B30509727 4LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1842.2
2.5°	1838.4
5°	1813.6
7.5°	1775.5
10°	1724.1
12.5°	1666.9
15°	1611.7
17.5°	1541.2
20°	1472.6
22.5°	1400.2
25°	1322.1
27.5°	1238.3
30°	1154.5
32.5°	1070.6
35°	990.6
37.5°	914.4
40°	842.0
42.5°	769.6
45°	699.2
47.5°	624.9
50°	548.7
52.5°	472.5
55°	396.3
57.5°	329.6
60°	261.0
62.5°	198.1
65°	144.8
67.5°	95.3
70°	55.2
72.5°	26.7
75°	7.6
77.5°	3.8
80°	1.9
82.5°	1.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)