

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212307

Luminaire Tested: **LSR4B40D010BZ EC4B30509727 4LBWLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212307  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B40D010BZ EC4B30509727 4LBWL1  
Description: PORTFOLIO 4 INCH CYLINDER  
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2890.4 lumens  
Efficiency: N/A  
Efficacy: 69.1 lumens/watt  
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212307

CATALOG NUMBER: LSR4B40D010BZ EC4B30509727 4LBWL11

### Luminous Intensity Polar Plot





TEST NUMBER: P212307

CATALOG NUMBER: LSR4B40D010BZ EC4B30509727 4LBWLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92																			
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84																			
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77																			
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70																			
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64																			
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58																			
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54																			
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49																			
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45																			
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212307

CATALOG NUMBER: LSR4B40D010BZ EC4B30509727 4LBWLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	173.2	6.0
10°-20°	546.6	18.9
20°-30°	852.7	29.5
30°-40°	829.6	28.7
40°-50°	414.3	14.3
50°-60°	64.1	2.2
60°-70°	7.7	0.3
70°-80°	2.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1572.4	54.4
0°-40°	2402.0	83.1
0°-60°	2880.5	99.7
0°-90°	2890.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2890.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1771	
5°	1794	173
15°	1930	547
25°	1874	853
35°	1347	830
45°	520	414
55°	53	64
65°	7	8
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P212307

CATALOG NUMBER: LSR4B40D010BZ EC4B30509727 4LBWLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1771.1
2.5°	1777.7
5°	1794.2
7.5°	1820.7
10°	1853.8
12.5°	1896.9
15°	1930.0
17.5°	1956.4
20°	1959.7
22.5°	1936.6
25°	1873.7
27.5°	1781.0
30°	1665.1
32.5°	1519.5
35°	1347.3
37.5°	1158.6
40°	960.0
42.5°	748.1
45°	519.7
47.5°	334.3
50°	201.9
52.5°	109.2
55°	53.0
57.5°	23.2
60°	13.2
62.5°	9.9
65°	6.6
67.5°	6.6
70°	3.3
72.5°	3.3
75°	3.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)