

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P430235

Luminaire Tested: **LAM4B212R509040DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P430235
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B212R509040DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 50 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2700.3 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.74
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct


Input Watts (W): 28.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P430235

CATALOG NUMBER: LAM4B212R509040DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P430235

CATALOG NUMBER: LAM4B212R509040DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|--|--|--|--|--|--|--|--|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | | | | | | | | | |
| RC | 80 | | | | | | | | | 70 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 | | | | | | | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 1 | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 95 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 2 | 110 | 105 | 102 | 99 | 107 | 104 | 100 | 98 | 100 | 98 | 96 | 97 | 95 | 93 | 95 | 93 | 92 | 90 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 3 | 105 | 99 | 95 | 92 | 103 | 98 | 94 | 91 | 95 | 92 | 89 | 93 | 90 | 88 | 91 | 89 | 87 | 85 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 4 | 101 | 94 | 89 | 86 | 99 | 93 | 89 | 85 | 91 | 87 | 84 | 89 | 86 | 83 | 87 | 84 | 82 | 81 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 5 | 96 | 89 | 84 | 80 | 95 | 88 | 84 | 80 | 87 | 83 | 79 | 85 | 81 | 79 | 84 | 80 | 78 | 77 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 6 | 92 | 85 | 80 | 76 | 91 | 84 | 79 | 76 | 83 | 78 | 75 | 81 | 77 | 75 | 80 | 77 | 74 | 73 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 7 | 89 | 81 | 75 | 72 | 87 | 80 | 75 | 72 | 79 | 74 | 71 | 78 | 74 | 71 | 77 | 73 | 71 | 69 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 8 | 85 | 77 | 72 | 68 | 84 | 76 | 71 | 68 | 75 | 71 | 68 | 74 | 70 | 67 | 73 | 70 | 67 | 66 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 9 | 82 | 73 | 68 | 65 | 81 | 73 | 68 | 65 | 72 | 68 | 64 | 71 | 67 | 64 | 70 | 67 | 64 | 63 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 10 | 79 | 70 | 65 | 62 | 78 | 70 | 65 | 62 | 69 | 64 | 61 | 68 | 64 | 61 | 68 | 64 | 61 | 60 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 713674 |
| 5° | 678978 |
| 10° | 659002 |
| 15° | 632306 |
| 20° | 520210 |
| 25° | 416808 |
| 30° | 217447 |
| 35° | 70133 |
| 40° | 11924 |
| 45° | 0 |
| 50° | 0 |
| 55° | 0 |
| 60° | 0 |
| 65° | 0 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P430235

CATALOG NUMBER: LAM4B212R509040DE010x1MMS

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 395.3 | 14.6 |
| 10°-20° | 1026.0 | 38.0 |
| 20°-30° | 998.2 | 37.0 |
| 30°-40° | 274.8 | 10.2 |
| 40°-50° | 6.0 | 0.2 |
| 50°-60° | 0.0 | 0.0 |
| 60°-70° | 0.0 | 0.0 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 2419.5 | 89.6 |
| 0°-40° | 2694.3 | 99.8 |
| 0°-60° | 2700.3 | 100.0 |
| 0°-90° | 2700.3 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2700.3 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 4430 | |
| 5° | 4198 | 395 |
| 15° | 3791 | 1026 |
| 25° | 2345 | 998 |
| 35° | 357 | 275 |
| 45° | 0 | 6 |
| 55° | 0 | 0 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P430235

CATALOG NUMBER: LAM4B212R509040DE010x1MMS

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 4429.9 |
| 2.5° | 4350.8 |
| 5° | 4198.5 |
| 7.5° | 4075.7 |
| 10° | 4028.4 |
| 12.5° | 4024.9 |
| 15° | 3791.1 |
| 17.5° | 3360.2 |
| 20° | 3034.3 |
| 22.5° | 2763.9 |
| 25° | 2344.8 |
| 27.5° | 1650.6 |
| 30° | 1168.9 |
| 32.5° | 707.2 |
| 35° | 356.6 |
| 37.5° | 159.4 |
| 40° | 56.7 |
| 42.5° | 4.7 |
| 45° | 0.0 |
| 47.5° | 0.0 |
| 50° | 0.0 |
| 52.5° | 0.0 |
| 55° | 0.0 |
| 57.5° | 0.0 |
| 60° | 0.0 |
| 62.5° | 0.0 |
| 65° | 0.0 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)