

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212312

Luminaire Tested: **LSR4B40D010BZ EC4B30508030 4LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212312
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30508030 4LBCSMW1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4265.1 lumens
Efficiency: N/A
Efficacy: 102.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212312

CATALOG NUMBER: LSR4B40D010BZ EC4B30508030 4LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P212312

CATALOG NUMBER: LSR4B40D010BZ EC4B30508030 4LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212312

CATALOG NUMBER: LSR4B40D010BZ EC4B30508030 4LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.0	3.9
10°-20°	469.9	11.0
20°-30°	706.8	16.6
30°-40°	837.7	19.6
40°-50°	833.6	19.5
50°-60°	672.0	15.8
60°-70°	406.6	9.5
70°-80°	150.9	3.5
80°-90°	22.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1341.8	31.5
0°-40°	2179.5	51.1
0°-60°	3685.1	86.4
0°-90°	4265.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4265.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1742	
5°	1734	165
15°	1664	470
25°	1535	707
35°	1341	838
45°	1086	834
55°	750	672
65°	408	407
75°	137	151
85°	18	23
90°	0	



TEST NUMBER: P212312

CATALOG NUMBER: LSR4B40D010BZ EC4B30508030 4LBCSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1742.0
2.5°	1742.0
5°	1734.2
7.5°	1729.1
10°	1713.6
12.5°	1687.7
15°	1664.5
17.5°	1638.6
20°	1607.6
22.5°	1576.6
25°	1535.2
27.5°	1491.3
30°	1442.2
32.5°	1395.7
35°	1341.4
37.5°	1284.5
40°	1217.3
42.5°	1152.7
45°	1085.5
47.5°	1010.6
50°	927.9
52.5°	842.6
55°	749.5
57.5°	666.8
60°	573.8
62.5°	491.1
65°	408.4
67.5°	330.8
70°	258.5
72.5°	193.8
75°	137.0
77.5°	87.9
80°	51.7
82.5°	31.0
85°	18.1
87.5°	7.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)