

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212336

Luminaire Tested: **LSR4B40D010BZ EC4B30508030 4LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212336
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30508030 4LBWL1
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4047.4 lumens
Efficiency: N/A
Efficacy: 96.8 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212336

CATALOG NUMBER: LSR4B40D010BZ EC4B30508030 4LBWL11

Luminous Intensity Polar Plot





TEST NUMBER: P212336

CATALOG NUMBER: LSR4B40D010BZ EC4B30508030 4LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92																																				
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84																																				
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77																																				
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70																																				
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64																																				
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58																																				
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54																																				
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49																																				
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45																																				
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212336

CATALOG NUMBER: LSR4B40D010BZ EC4B30508030 4LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	242.5	6.0
10°-20°	765.3	18.9
20°-30°	1193.9	29.5
30°-40°	1161.7	28.7
40°-50°	580.2	14.3
50°-60°	89.8	2.2
60°-70°	10.9	0.3
70°-80°	3.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2201.8	54.4
0°-40°	3363.5	83.1
0°-60°	4033.5	99.7
0°-90°	4047.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4047.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2480	
5°	2512	243
15°	2702	765
25°	2624	1194
35°	1887	1162
45°	728	580
55°	74	90
65°	9	11
75°	5	3
85°	0	0
90°	0	



TEST NUMBER: P212336

CATALOG NUMBER: LSR4B40D010BZ EC4B30508030 4LBWLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2479.9
2.5°	2489.2
5°	2512.4
7.5°	2549.4
10°	2595.8
12.5°	2656.1
15°	2702.4
17.5°	2739.5
20°	2744.1
22.5°	2711.7
25°	2623.6
27.5°	2493.8
30°	2331.6
32.5°	2127.6
35°	1886.6
37.5°	1622.4
40°	1344.3
42.5°	1047.6
45°	727.7
47.5°	468.2
50°	282.8
52.5°	153.0
55°	74.2
57.5°	32.4
60°	18.5
62.5°	13.9
65°	9.3
67.5°	9.3
70°	4.6
72.5°	4.6
75°	4.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)