

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431438

Luminaire Tested: **LAMR4B212R609050DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P431438
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B212R609050DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2305.7 lumens
Efficiency: N/A
Efficacy: 81.2 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 28.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P431438

CATALOG NUMBER: LAMR4B212R609050DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P431438

CATALOG NUMBER: LAMR4B212R609050DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82			
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77			
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	69	67			
7	84	75	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63			
8	80	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	60	59			
9	77	67	62	58	76	67	61	58	66	61	57	65	60	57	64	60	57	56			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1307456
5°	1263617
10°	1251826
15°	1220774
20°	1126638
25°	1008907
30°	780725
35°	467690
40°	179693
45°	65658
50°	2610
55°	1892
60°	2171
65°	1284
70°	1587
75°	2097
80°	3125
85°	0



TEST NUMBER: P431438

CATALOG NUMBER: LAMR4B212R609050DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	242.3	10.5
10°-20°	664.9	28.8
20°-30°	829.5	36.0
30°-40°	483.2	21.0
40°-50°	80.7	3.5
50°-60°	2.1	0.1
60°-70°	1.5	0.1
70°-80°	1.2	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1736.6	75.3
0°-40°	2219.8	96.3
0°-60°	2302.6	99.9
0°-90°	2305.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2305.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2650	
5°	2551	242
15°	2390	665
25°	1853	829
35°	776	483
45°	94	81
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P431438

CATALOG NUMBER: LAMR4B212R609050DE010x1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2650.0
2.5°	2606.3
5°	2551.4
7.5°	2520.0
10°	2498.7
12.5°	2464.0
15°	2390.0
17.5°	2279.1
20°	2145.8
22.5°	2010.2
25°	1853.3
27.5°	1635.9
30°	1370.4
32.5°	1073.4
35°	776.5
37.5°	489.7
40°	279.0
42.5°	163.6
45°	94.1
47.5°	32.5
50°	3.4
52.5°	2.2
55°	2.2
57.5°	2.2
60°	2.2
62.5°	2.2
65°	1.1
67.5°	1.1
70°	1.1
72.5°	1.1
75°	1.1
77.5°	1.1
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)