

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212384

Luminaire Tested: **LSR4B40D010BZ EC4B30509730 4LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212384
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30509730 4LBSB1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2634.1 lumens
Efficiency: N/A
Efficacy: 63.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212384

CATALOG NUMBER: LSR4B40D010BZ EC4B30509730 4LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P212384

CATALOG NUMBER: LSR4B40D010BZ EC4B30509730 4LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 111 | 107 | 103 | 100 | 108 | 105 | 101 | 98 | 100 | 98 | 95 | 97 | 94 | 93 | 93 | 91 | 90 | 88 | | | | | | | | | | | | | | | | | | | |
| 2 | 102 | 95 | 89 | 84 | 100 | 93 | 88 | 83 | 90 | 85 | 81 | 86 | 83 | 79 | 84 | 80 | 78 | 76 | | | | | | | | | | | | | | | | | | | |
| 3 | 94 | 84 | 77 | 72 | 91 | 83 | 76 | 71 | 80 | 74 | 70 | 77 | 73 | 68 | 75 | 71 | 67 | 65 | | | | | | | | | | | | | | | | | | | |
| 4 | 86 | 76 | 68 | 62 | 84 | 74 | 67 | 61 | 72 | 65 | 60 | 70 | 64 | 60 | 68 | 63 | 59 | 57 | | | | | | | | | | | | | | | | | | | |
| 5 | 80 | 68 | 60 | 54 | 78 | 67 | 59 | 53 | 65 | 58 | 53 | 63 | 57 | 52 | 61 | 56 | 52 | 50 | | | | | | | | | | | | | | | | | | | |
| 6 | 74 | 62 | 53 | 47 | 72 | 61 | 53 | 47 | 59 | 52 | 47 | 57 | 51 | 46 | 56 | 50 | 46 | 44 | | | | | | | | | | | | | | | | | | | |
| 7 | 69 | 56 | 48 | 42 | 67 | 55 | 48 | 42 | 54 | 47 | 42 | 52 | 46 | 41 | 51 | 45 | 41 | 39 | | | | | | | | | | | | | | | | | | | |
| 8 | 64 | 51 | 43 | 38 | 63 | 51 | 43 | 38 | 49 | 42 | 37 | 48 | 42 | 37 | 47 | 41 | 37 | 35 | | | | | | | | | | | | | | | | | | | |
| 9 | 60 | 47 | 39 | 34 | 59 | 47 | 39 | 34 | 46 | 39 | 34 | 45 | 38 | 34 | 44 | 38 | 34 | 32 | | | | | | | | | | | | | | | | | | | |
| 10 | 56 | 44 | 36 | 31 | 55 | 43 | 36 | 31 | 42 | 36 | 31 | 41 | 35 | 31 | 40 | 35 | 31 | 29 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212384

CATALOG NUMBER: LSR4B40D010BZ EC4B30509730 4LBSB1

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 109.7 | 4.2 |
| 10°-20° | 311.2 | 11.8 |
| 20°-30° | 462.9 | 17.6 |
| 30°-40° | 538.7 | 20.4 |
| 40°-50° | 525.0 | 19.9 |
| 50°-60° | 403.8 | 15.3 |
| 60°-70° | 223.2 | 8.5 |
| 70°-80° | 59.1 | 2.2 |
| 80°-90° | 0.4 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 883.7 | 33.6 |
| 0°-40° | 1422.4 | 54.0 |
| 0°-60° | 2351.3 | 89.3 |
| 0°-90° | 2634.1 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2634.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1162 | |
| 5° | 1155 | 110 |
| 15° | 1102 | 311 |
| 25° | 1005 | 463 |
| 35° | 865 | 539 |
| 45° | 681 | 525 |
| 55° | 451 | 404 |
| 65° | 224 | 223 |
| 75° | 50 | 59 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P212384

CATALOG NUMBER: LSR4B40D010BZ EC4B30509730 4LBSB1

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1162.0 |
| 2.5° | 1162.0 |
| 5° | 1155.3 |
| 7.5° | 1145.3 |
| 10° | 1138.6 |
| 12.5° | 1118.6 |
| 15° | 1101.9 |
| 17.5° | 1085.2 |
| 20° | 1061.8 |
| 22.5° | 1038.4 |
| 25° | 1005.0 |
| 27.5° | 971.7 |
| 30° | 938.3 |
| 32.5° | 901.5 |
| 35° | 864.8 |
| 37.5° | 818.1 |
| 40° | 778.0 |
| 42.5° | 734.6 |
| 45° | 681.2 |
| 47.5° | 631.1 |
| 50° | 574.3 |
| 52.5° | 514.2 |
| 55° | 450.8 |
| 57.5° | 390.7 |
| 60° | 333.9 |
| 62.5° | 277.1 |
| 65° | 223.7 |
| 67.5° | 173.6 |
| 70° | 126.9 |
| 72.5° | 86.8 |
| 75° | 50.1 |
| 77.5° | 23.4 |
| 80° | 3.3 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)