

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212408

Luminaire Tested: **LSR4B40D010BZ EC4B30508035 4LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212408
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30508035 4LBNGPH1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1962.2 lumens
Efficiency: N/A
Efficacy: 46.9 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212408

CATALOG NUMBER: LSR4B40D010BZ EC4B30508035 4LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P212408

CATALOG NUMBER: LSR4B40D010BZ EC4B30508035 4LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 | 101 | 100 | 98 | 97 | 96 | 95 | 94 | | | |
| 2 | 108 | 103 | 99 | 96 | 106 | 101 | 98 | 95 | 98 | 95 | 93 | 95 | 93 | 91 | 92 | 91 | 89 | 87 | | | |
| 3 | 103 | 96 | 91 | 87 | 101 | 95 | 90 | 87 | 92 | 88 | 85 | 90 | 87 | 84 | 88 | 85 | 83 | 81 | | | |
| 4 | 97 | 90 | 84 | 80 | 96 | 89 | 84 | 80 | 87 | 82 | 79 | 85 | 81 | 78 | 83 | 80 | 77 | 76 | | | |
| 5 | 93 | 84 | 78 | 74 | 91 | 83 | 78 | 74 | 82 | 77 | 73 | 80 | 76 | 73 | 78 | 75 | 72 | 70 | | | |
| 6 | 88 | 79 | 73 | 69 | 86 | 78 | 73 | 69 | 77 | 72 | 68 | 75 | 71 | 68 | 74 | 70 | 67 | 66 | | | |
| 7 | 84 | 74 | 68 | 64 | 82 | 74 | 68 | 64 | 72 | 67 | 64 | 71 | 67 | 63 | 70 | 66 | 63 | 62 | | | |
| 8 | 80 | 70 | 64 | 60 | 78 | 70 | 64 | 60 | 68 | 63 | 60 | 67 | 63 | 59 | 66 | 62 | 59 | 58 | | | |
| 9 | 76 | 66 | 60 | 56 | 75 | 66 | 60 | 56 | 65 | 60 | 56 | 64 | 59 | 56 | 63 | 59 | 56 | 54 | | | |
| 10 | 72 | 63 | 57 | 53 | 71 | 62 | 57 | 53 | 61 | 56 | 53 | 61 | 56 | 53 | 60 | 56 | 52 | 51 | | | |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212408

CATALOG NUMBER: LSR4B40D010BZ EC4B30508035 4LBNGPH1

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 213.9 | 10.9 |
| 10°-20° | 536.3 | 27.3 |
| 20°-30° | 653.6 | 33.3 |
| 30°-40° | 431.2 | 22.0 |
| 40°-50° | 99.3 | 5.1 |
| 50°-60° | 19.0 | 1.0 |
| 60°-70° | 7.0 | 0.4 |
| 70°-80° | 1.9 | 0.1 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1403.8 | 71.5 |
| 0°-40° | 1835.0 | 93.5 |
| 0°-60° | 1953.3 | 99.5 |
| 0°-90° | 1962.2 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1962.2 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2353 | |
| 5° | 2296 | 214 |
| 15° | 1920 | 536 |
| 25° | 1436 | 654 |
| 35° | 689 | 431 |
| 45° | 109 | 99 |
| 55° | 19 | 19 |
| 65° | 5 | 7 |
| 75° | 0 | 2 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P212408

CATALOG NUMBER: LSR4B40D010BZ EC4B30508035 4LBNGPH1

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 2353.0 |
| 2.5° | 2348.3 |
| 5° | 2296.0 |
| 7.5° | 2224.7 |
| 10° | 2129.6 |
| 12.5° | 2034.5 |
| 15° | 1920.5 |
| 17.5° | 1801.6 |
| 20° | 1678.0 |
| 22.5° | 1568.7 |
| 25° | 1435.6 |
| 27.5° | 1302.5 |
| 30° | 1131.4 |
| 32.5° | 922.2 |
| 35° | 689.3 |
| 37.5° | 480.1 |
| 40° | 309.0 |
| 42.5° | 190.1 |
| 45° | 109.3 |
| 47.5° | 57.0 |
| 50° | 33.3 |
| 52.5° | 28.5 |
| 55° | 19.0 |
| 57.5° | 14.3 |
| 60° | 14.3 |
| 62.5° | 9.5 |
| 65° | 4.8 |
| 67.5° | 4.8 |
| 70° | 4.8 |
| 72.5° | 4.8 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)