

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212423

Luminaire Tested: **LSR4B40D010BZ EC4B30508035 4LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212423
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30508035 4LBWH1
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3501.5 lumens
Efficiency: N/A
Efficacy: 83.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212423

CATALOG NUMBER: LSR4B40D010BZ EC4B30508035 4LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P212423

CATALOG NUMBER: LSR4B40D010BZ EC4B30508035 4LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212423

CATALOG NUMBER: LSR4B40D010BZ EC4B30508035 4LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.9	6.1
10°-20°	619.3	17.7
20°-30°	913.9	26.1
30°-40°	901.8	25.8
40°-50°	551.9	15.8
50°-60°	211.6	6.0
60°-70°	66.1	1.9
70°-80°	19.4	0.6
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1748.1	49.9
0°-40°	2649.9	75.7
0°-60°	3413.4	97.5
0°-90°	3501.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3501.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2257	
5°	2257	215
15°	2195	619
25°	2000	914
35°	1463	902
45°	708	552
55°	223	212
65°	62	66
75°	19	19
85°	0	3
90°	0	



TEST NUMBER: P212423

CATALOG NUMBER: LSR4B40D010BZ EC4B30508035 4LBWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2256.9
2.5°	2261.6
5°	2256.9
7.5°	2252.1
10°	2237.9
12.5°	2218.9
15°	2195.1
17.5°	2166.6
20°	2123.8
22.5°	2076.3
25°	2000.3
27.5°	1905.3
30°	1786.5
32.5°	1639.2
35°	1463.4
37.5°	1268.6
40°	1069.0
42.5°	883.7
45°	707.9
47.5°	551.2
50°	418.1
52.5°	308.8
55°	223.3
57.5°	156.8
60°	114.0
62.5°	85.5
65°	61.8
67.5°	47.5
70°	33.3
72.5°	23.8
75°	19.0
77.5°	9.5
80°	9.5
82.5°	4.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)