

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212430

Luminaire Tested: **LSR4B40D010BZ EC4B30509035 4LBMGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212430  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B40D010BZ EC4B30509035 4LBMGPH1  
Description: PORTFOLIO 4 INCH CYLINDER  
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1911.6 lumens  
Efficiency: N/A  
Efficacy: 45.7 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.92  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212430

CATALOG NUMBER: LSR4B40D010BZ EC4B30509035 4LBMGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P212430

CATALOG NUMBER: LSR4B40D010BZ EC4B30509035 4LBMGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	88	86																			
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79																			
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73																			
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68																			
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63																			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59																			
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55																			
9	73	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	52	51																			
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212430

CATALOG NUMBER: LSR4B40D010BZ EC4B30509035 4LBMGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	180.8	9.5
10°-20°	471.6	24.7
20°-30°	604.9	31.6
30°-40°	437.2	22.9
40°-50°	156.8	8.2
50°-60°	42.3	2.2
60°-70°	13.8	0.7
70°-80°	4.2	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1257.3	65.8
0°-40°	1694.5	88.6
0°-60°	1893.6	99.1
0°-90°	1911.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1911.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1965	
5°	1929	181
15°	1680	472
25°	1334	605
35°	699	437
45°	189	157
55°	44	42
65°	12	14
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P212430

CATALOG NUMBER: LSR4B40D010BZ EC4B30509035 4LBMGPH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1965.3
2.5°	1957.3
5°	1929.2
7.5°	1885.0
10°	1824.7
12.5°	1756.4
15°	1680.0
17.5°	1603.6
20°	1527.3
22.5°	1438.8
25°	1334.3
27.5°	1213.8
30°	1061.0
32.5°	884.2
35°	699.3
37.5°	530.5
40°	385.8
42.5°	273.3
45°	188.9
47.5°	128.6
50°	84.4
52.5°	60.3
55°	44.2
57.5°	32.2
60°	24.1
62.5°	20.1
65°	12.1
67.5°	8.0
70°	8.0
72.5°	4.0
75°	4.0
77.5°	4.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)