

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431397

Luminaire Tested: **LAMR4B212R509730DE010x1MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P431397
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B212R509730DE010x1MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 50 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2364.8 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.74
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct


Input Watts (W): 28.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P431397

CATALOG NUMBER: LAMR4B212R509730DE010x1MW

Luminous Intensity Polar Plot





TEST NUMBER: P431397

CATALOG NUMBER: LAMR4B212R509730DE010x1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																																				
2	110	105	102	99	107	104	100	98	100	98	96	97	95	93	95	93	92	90																																				
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85																																				
4	101	94	89	86	99	93	89	85	91	87	84	89	86	83	87	84	82	81																																				
5	96	89	84	80	95	88	84	80	87	83	79	85	81	79	84	80	78	77																																				
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73																																				
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69																																				
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66																																				
9	82	73	68	65	81	73	68	65	72	68	64	71	67	64	70	67	64	63																																				
10	79	70	65	62	78	70	65	62	69	64	61	68	64	61	68	64	61	60																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	625018
5°	594625
10°	577142
15°	553766
20°	455593
25°	365027
30°	190435
35°	61420
40°	10431
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P431397

CATALOG NUMBER: LAMR4B212R509730DE010x1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	346.2	14.6
10°-20°	898.6	38.0
20°-30°	874.2	37.0
30°-40°	240.6	10.2
40°-50°	5.2	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2119.0	89.6
0°-40°	2359.6	99.8
0°-60°	2364.8	100.0
0°-90°	2364.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2364.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3880	
5°	3677	346
15°	3320	899
25°	2054	874
35°	312	241
45°	0	5
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P431397

CATALOG NUMBER: LAMR4B212R509730DE010x1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3879.6
2.5°	3810.3
5°	3676.9
7.5°	3569.4
10°	3528.0
12.5°	3524.9
15°	3320.2
17.5°	2942.8
20°	2657.4
22.5°	2420.6
25°	2053.5
27.5°	1445.5
30°	1023.7
32.5°	619.4
35°	312.3
37.5°	139.6
40°	49.6
42.5°	4.1
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)