

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212461

Luminaire Tested: **LSR4B40D010BZ EC4B30508040 4LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212461
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30508040 4LBML1
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3971.5 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212461
CATALOG NUMBER: LSR4B40D010BZ EC4B30508040 4LBML11

Luminous Intensity Polar Plot





TEST NUMBER: P212461

CATALOG NUMBER: LSR4B40D010BZ EC4B30508040 4LBML11

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88																			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83																			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78																			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73																			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69																			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65																			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62																			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58																			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212461

CATALOG NUMBER: LSR4B40D010BZ EC4B30508040 4LBML11

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	566.9	14.3
10°-20°	1267.4	31.9
20°-30°	1260.0	31.7
30°-40°	686.2	17.3
40°-50°	158.6	4.0
50°-60°	22.3	0.6
60°-70°	8.3	0.2
70°-80°	1.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3094.3	77.9
0°-40°	3780.5	95.2
0°-60°	3961.4	99.7
0°-90°	3971.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3971.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6261	
5°	6131	567
15°	4574	1267
25°	2763	1260
35°	1062	686
45°	183	159
55°	24	22
65°	10	8
75°	0	2
85°	0	0
90°	0	



TEST NUMBER: P212461

CATALOG NUMBER: LSR4B40D010BZ EC4B30508040 4LBML11

CANDELA DISTRIBUTION (FULL):

	0°
0°	6261.0
2.5°	6246.6
5°	6131.3
7.5°	5895.8
10°	5569.1
12.5°	5088.6
15°	4574.4
17.5°	4065.1
20°	3565.4
22.5°	3156.9
25°	2762.9
27.5°	2388.1
30°	1965.3
32.5°	1494.4
35°	1061.9
37.5°	716.0
40°	466.1
42.5°	293.1
45°	182.6
47.5°	105.7
50°	52.9
52.5°	28.8
55°	24.0
57.5°	14.4
60°	14.4
62.5°	9.6
65°	9.6
67.5°	4.8
70°	4.8
72.5°	4.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)