

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212465

Luminaire Tested: **LSR4B40D010BZ EC4B30508040 4LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212465
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30508040 4LBNGPH1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1983.3 lumens
Efficiency: N/A
Efficacy: 47.4 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212465
CATALOG NUMBER: LSR4B40D010BZ EC4B30508040 4LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P212465

CATALOG NUMBER: LSR4B40D010BZ EC4B30508040 4LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	52	51			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212465

CATALOG NUMBER: LSR4B40D010BZ EC4B30508040 4LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	216.3	10.9
10°-20°	542.1	27.3
20°-30°	660.7	33.3
30°-40°	435.9	22.0
40°-50°	100.3	5.1
50°-60°	19.2	1.0
60°-70°	7.1	0.4
70°-80°	1.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1419.0	71.5
0°-40°	1854.8	93.5
0°-60°	1974.4	99.5
0°-90°	1983.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1983.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2378	
5°	2321	216
15°	1941	542
25°	1451	661
35°	697	436
45°	110	100
55°	19	19
65°	5	7
75°	0	2
85°	0	0
90°	0	



TEST NUMBER: P212465

CATALOG NUMBER: LSR4B40D010BZ EC4B30508040 4LBNGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2378.5
2.5°	2373.7
5°	2320.8
7.5°	2248.7
10°	2152.6
12.5°	2056.5
15°	1941.2
17.5°	1821.1
20°	1696.2
22.5°	1585.6
25°	1451.1
27.5°	1316.6
30°	1143.6
32.5°	932.2
35°	696.7
37.5°	485.3
40°	312.3
42.5°	192.2
45°	110.5
47.5°	57.7
50°	33.6
52.5°	28.8
55°	19.2
57.5°	14.4
60°	14.4
62.5°	9.6
65°	4.8
67.5°	4.8
70°	4.8
72.5°	4.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)