

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212486

Luminaire Tested: **LSR4B40D010BZ EC4B30509040 4LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212486
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30509040 4LBCSMW1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3700.9 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212486

CATALOG NUMBER: LSR4B40D010BZ EC4B30509040 4LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P212486

CATALOG NUMBER: LSR4B40D010BZ EC4B30509040 4LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212486

CATALOG NUMBER: LSR4B40D010BZ EC4B30509040 4LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.2	3.9
10°-20°	407.7	11.0
20°-30°	613.3	16.6
30°-40°	726.9	19.6
40°-50°	723.4	19.5
50°-60°	583.1	15.8
60°-70°	352.8	9.5
70°-80°	131.0	3.5
80°-90°	19.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1164.3	31.5
0°-40°	1891.1	51.1
0°-60°	3197.6	86.4
0°-90°	3700.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3700.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1512	
5°	1505	143
15°	1444	408
25°	1332	613
35°	1164	727
45°	942	723
55°	650	583
65°	354	353
75°	119	131
85°	16	20
90°	0	



TEST NUMBER: P212486

CATALOG NUMBER: LSR4B40D010BZ EC4B30509040 4LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1511.6
2.5°	1511.6
5°	1504.8
7.5°	1500.3
10°	1486.9
12.5°	1464.5
15°	1444.3
17.5°	1421.9
20°	1394.9
22.5°	1368.0
25°	1332.1
27.5°	1294.0
30°	1251.4
32.5°	1211.0
35°	1163.9
37.5°	1114.6
40°	1056.3
42.5°	1000.2
45°	941.9
47.5°	876.9
50°	805.1
52.5°	731.1
55°	650.4
57.5°	578.6
60°	497.9
62.5°	426.1
65°	354.3
67.5°	287.1
70°	224.3
72.5°	168.2
75°	118.9
77.5°	76.3
80°	44.9
82.5°	26.9
85°	15.7
87.5°	6.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)