

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212502

Luminaire Tested: **LSR4B40D010BZ EC4B30509040 4LBSH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212502  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B40D010BZ EC4B30509040 4LBSH1  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3483.3 lumens  
Efficiency: N/A  
Efficacy: 83.3 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212502

CATALOG NUMBER: LSR4B40D010BZ EC4B30509040 4LBSH1

### Luminous Intensity Polar Plot





TEST NUMBER: P212502

CATALOG NUMBER: LSR4B40D010BZ EC4B30509040 4LBSH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212502

CATALOG NUMBER: LSR4B40D010BZ EC4B30509040 4LBSH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	170.6	4.9
10°-20°	463.8	13.3
20°-30°	644.1	18.5
30°-40°	702.9	20.2
40°-50°	655.7	18.8
50°-60°	497.7	14.3
60°-70°	272.5	7.8
70°-80°	75.0	2.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1278.5	36.7
0°-40°	1981.4	56.9
0°-60°	3134.8	90.0
0°-90°	3483.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3483.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1822	
5°	1806	171
15°	1653	464
25°	1400	644
35°	1124	703
45°	851	656
55°	556	498
65°	272	272
75°	65	75
85°	0	1
90°	0	



TEST NUMBER: P212502

CATALOG NUMBER: LSR4B40D010BZ EC4B30509040 4LBSH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1821.8
2.5°	1821.8
5°	1806.4
7.5°	1783.4
10°	1748.9
12.5°	1702.9
15°	1653.0
17.5°	1591.6
20°	1534.1
22.5°	1465.1
25°	1399.9
27.5°	1334.7
30°	1261.8
32.5°	1192.8
35°	1123.7
37.5°	1054.7
40°	989.5
42.5°	920.5
45°	851.4
47.5°	782.4
50°	705.7
52.5°	632.8
55°	556.1
57.5°	483.2
60°	410.4
62.5°	337.5
65°	272.3
67.5°	210.9
70°	157.2
72.5°	107.4
75°	65.2
77.5°	30.7
80°	7.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)