

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212532

Luminaire Tested: **LSR4B40D010BZ EC4B30508050 4LBSLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212532  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B40D010BZ EC4B30508050 4LBSLI1  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4334.1 lumens  
Efficiency: N/A  
Efficacy: 103.7 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212532

CATALOG NUMBER: LSR4B40D010BZ EC4B30508050 4LBSLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P212532

CATALOG NUMBER: LSR4B40D010BZ EC4B30508050 4LBSLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90																			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80																			
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71																			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63																			
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57																			
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51																			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46																			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42																			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39																			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212532

CATALOG NUMBER: LSR4B40D010BZ EC4B30508050 4LBSLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	280.6	6.5
10°-20°	715.6	16.5
20°-30°	927.3	21.4
30°-40°	908.6	21.0
40°-50°	770.2	17.8
50°-60°	504.9	11.6
60°-70°	202.9	4.7
70°-80°	23.2	0.5
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1923.6	44.4
0°-40°	2832.2	65.3
0°-60°	4107.3	94.8
0°-90°	4334.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4334.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3095	
5°	3013	281
15°	2552	716
25°	2025	927
35°	1444	909
45°	1003	770
55°	561	505
65°	197	203
75°	10	23
85°	0	1
90°	0	



TEST NUMBER: P212532

CATALOG NUMBER: LSR4B40D010BZ EC4B30508050 4LBSLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3094.6
2.5°	3070.7
5°	3013.1
7.5°	2917.1
10°	2797.2
12.5°	2667.6
15°	2552.5
17.5°	2427.7
20°	2303.0
22.5°	2168.7
25°	2024.7
27.5°	1876.0
30°	1722.4
32.5°	1578.5
35°	1444.2
37.5°	1333.8
40°	1213.9
42.5°	1108.3
45°	1002.8
47.5°	892.4
50°	782.1
52.5°	671.7
55°	561.4
57.5°	460.6
60°	364.6
62.5°	278.3
65°	196.7
67.5°	129.5
70°	76.8
72.5°	33.6
75°	9.6
77.5°	4.8
80°	4.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)