

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212562

Luminaire Tested: **LSR4B40D010BZ EC4B30509050 4LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212562
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30509050 4LBSMW1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3648.5 lumens
Efficiency: N/A
Efficacy: 87.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212562

CATALOG NUMBER: LSR4B40D010BZ EC4B30509050 4LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P212562

CATALOG NUMBER: LSR4B40D010BZ EC4B30509050 4LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																			
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212562

CATALOG NUMBER: LSR4B40D010BZ EC4B30509050 4LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.3	3.8
10°-20°	397.0	10.9
20°-30°	598.0	16.4
30°-40°	711.5	19.5
40°-50°	710.2	19.5
50°-60°	577.6	15.8
60°-70°	355.3	9.7
70°-80°	137.6	3.8
80°-90°	22.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1134.3	31.1
0°-40°	1845.8	50.6
0°-60°	3133.5	85.9
0°-90°	3648.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3648.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1470	
5°	1466	139
15°	1410	397
25°	1301	598
35°	1139	712
45°	923	710
55°	646	578
65°	357	355
75°	125	138
85°	17	22
90°	0	



TEST NUMBER: P212562

CATALOG NUMBER: LSR4B40D010BZ EC4B30509050 4LBSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1470.0
2.5°	1472.2
5°	1465.7
7.5°	1457.0
10°	1446.2
12.5°	1426.8
15°	1409.5
17.5°	1383.5
20°	1355.4
22.5°	1329.5
25°	1301.4
27.5°	1262.5
30°	1223.6
32.5°	1186.8
35°	1139.3
37.5°	1087.4
40°	1039.8
42.5°	981.4
45°	923.1
47.5°	860.4
50°	793.4
52.5°	724.2
55°	646.4
57.5°	570.7
60°	497.2
62.5°	425.9
65°	356.7
67.5°	291.8
70°	231.3
72.5°	175.1
75°	125.4
77.5°	82.1
80°	49.7
82.5°	30.3
85°	17.3
87.5°	8.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)