

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212564

Luminaire Tested: **LSR4B40D010BZ EC4B30509050 4LBSWMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212564  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B40D010BZ EC4B30509050 4LBSWMH1  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3546.9 lumens  
Efficiency: N/A  
Efficacy: 84.9 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212564

CATALOG NUMBER: LSR4B40D010BZ EC4B30509050 4LBSWMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P212564

CATALOG NUMBER: LSR4B40D010BZ EC4B30509050 4LBSWMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79
3	96	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212564

CATALOG NUMBER: LSR4B40D010BZ EC4B30509050 4LBSWMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	207.8	5.9
10°-20°	550.6	15.5
20°-30°	739.5	20.8
30°-40°	756.9	21.3
40°-50°	655.2	18.5
50°-60°	435.8	12.3
60°-70°	179.0	5.0
70°-80°	21.2	0.6
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1497.9	42.2
0°-40°	2254.8	63.6
0°-60°	3345.8	94.3
0°-90°	3546.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3546.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2248	
5°	2213	208
15°	1967	551
25°	1613	739
35°	1209	757
45°	853	655
55°	484	436
65°	177	179
75°	9	21
85°	0	1
90°	0	



TEST NUMBER: P212564

CATALOG NUMBER: LSR4B40D010BZ EC4B30509050 4LBSWMH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2248.1
2.5°	2243.4
5°	2213.2
7.5°	2166.7
10°	2103.9
12.5°	2034.2
15°	1966.8
17.5°	1880.7
20°	1797.1
22.5°	1708.7
25°	1613.4
27.5°	1511.1
30°	1408.8
32.5°	1306.5
35°	1208.9
37.5°	1115.9
40°	1027.6
42.5°	939.2
45°	853.2
47.5°	762.5
50°	669.5
52.5°	576.5
55°	483.6
57.5°	402.2
60°	318.5
62.5°	241.8
65°	176.7
67.5°	116.2
70°	67.4
72.5°	32.5
75°	9.3
77.5°	4.6
80°	2.3
82.5°	2.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)