

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P429911

Luminaire Tested: **LAM4B112R459024DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P429911
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2008-908-8)
Test Lab: INNOVATION CENTER (G2)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B112R459024DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 45 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1046.4 lumens
Efficiency: N/A
Efficacy: 73.2 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.66
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P429911

CATALOG NUMBER: LAM4B112R459024DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P429911

CATALOG NUMBER: LAM4B112R459024DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89	89	89	89
3	105	99	94	91	103	98	93	90	95	92	89	93	90	87	90	88	86	85	85	85	85
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80	80	80	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	76	76	76
6	92	85	79	76	91	84	79	75	82	78	75	81	77	74	80	77	74	73	73	73	73
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69	69	69	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66	66	66	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	65	63	63	63	63
10	79	71	66	62	78	70	66	62	70	65	62	69	65	62	68	65	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	966925
5°	966607
10°	918767
15°	807090
20°	617399
25°	360437
30°	147497
35°	62399
40°	34006
45°	21979
50°	17117
55°	14881
60°	12038
65°	9456
70°	8800
75°	7816
80°	8524
85°	5661



TEST NUMBER: P429911

CATALOG NUMBER: LAM4B112R459024DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.6	17.5
10°-20°	430.2	41.1
20°-30°	303.1	29.0
30°-40°	74.6	7.1
40°-50°	26.0	2.5
50°-60°	15.4	1.5
60°-70°	8.5	0.8
70°-80°	4.7	0.5
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	915.9	87.5
0°-40°	990.5	94.7
0°-60°	1031.9	98.6
0°-90°	1046.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1046.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1960	
5°	1952	183
15°	1580	430
25°	662	303
35°	104	75
45°	32	26
55°	17	15
65°	8	9
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P429911

CATALOG NUMBER: LAM4B112R459024DE010x1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1959.8
2.5°	1954.8
5°	1951.7
7.5°	1916.2
10°	1833.9
12.5°	1722.2
15°	1580.1
17.5°	1396.3
20°	1175.9
22.5°	923.1
25°	662.1
27.5°	427.5
30°	258.9
32.5°	157.4
35°	103.6
37.5°	73.1
40°	52.8
42.5°	40.6
45°	31.5
47.5°	26.4
50°	22.3
52.5°	19.3
55°	17.3
57.5°	15.2
60°	12.2
62.5°	10.2
65°	8.1
67.5°	7.1
70°	6.1
72.5°	5.1
75°	4.1
77.5°	4.1
80°	3.0
82.5°	2.0
85°	1.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)