

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P430427

Luminaire Tested: **LAM4B312R309040DE01021MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P430427
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B312R309040DE01021MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 30 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3911.8 lumens
Efficiency: N/A
Efficacy: 95.6 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P430427

CATALOG NUMBER: LAM4B312R309040DE01021MMS

Luminous Intensity Polar Plot





TEST NUMBER: P430427

CATALOG NUMBER: LAM4B312R309040DE01021MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96
2	111	107	104	102	109	106	103	100	102	100	98	100	98	96	97	95	94	93
3	107	103	99	96	105	101	98	95	99	96	94	96	94	92	94	92	91	90
4	104	98	94	91	102	97	94	91	95	92	90	93	91	89	92	90	88	87
5	101	95	91	87	99	94	90	87	92	89	86	91	88	86	89	87	85	84
6	98	91	87	84	97	91	87	84	89	86	83	88	85	83	87	84	82	81
7	95	88	84	81	94	88	84	81	87	83	81	86	83	80	85	82	80	79
8	92	86	81	79	91	85	81	78	84	81	78	83	80	78	83	80	78	77
9	90	83	79	76	89	83	79	76	82	78	76	81	78	76	80	78	75	74
10	88	81	77	74	87	80	77	74	80	76	74	79	76	74	78	76	73	72

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7087693
5°	6932857
10°	6011137
15°	3725710
20°	1365533
25°	456466
30°	224065
35°	111728
40°	69301
45°	44028
50°	31317
55°	25547
60°	22005
65°	17278
70°	21350
75°	21160
80°	21025
85°	20945



TEST NUMBER: P430427

CATALOG NUMBER: LAM4B312R309040DE01021MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1275.8	32.6
10°-20°	1926.1	49.2
20°-30°	469.6	12.0
30°-40°	128.6	3.3
40°-50°	51.8	1.3
50°-60°	27.7	0.7
60°-70°	16.5	0.4
70°-80°	12.7	0.3
80°-90°	3.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3671.5	93.9
0°-40°	3800.1	97.1
0°-60°	3879.5	99.2
0°-90°	3911.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3911.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14366	
5°	13998	###
15°	7294	1926
25°	838	470
35°	186	129
45°	63	52
55°	30	28
65°	15	17
75°	11	13
85°	4	3
90°	0	



TEST NUMBER: P430427

CATALOG NUMBER: LAM4B312R309040DE01021MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	14365.6
2.5°	14269.1
5°	13998.3
7.5°	13352.7
10°	11998.5
12.5°	9876.4
15°	7294.1
17.5°	4700.7
20°	2600.8
22.5°	1387.6
25°	838.5
27.5°	567.6
30°	393.3
32.5°	267.1
35°	185.5
37.5°	137.3
40°	107.6
42.5°	81.6
45°	63.1
47.5°	51.9
50°	40.8
52.5°	37.1
55°	29.7
57.5°	26.0
60°	22.3
62.5°	18.6
65°	14.8
67.5°	14.8
70°	14.8
72.5°	14.8
75°	11.1
77.5°	11.1
80°	7.4
82.5°	3.7
85°	3.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)