

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431088

Luminaire Tested: **LAMR4B112R509024DE010x1MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P431088
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B112R509024DE010x1MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 50 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1124.4 lumens
Efficiency: N/A
Efficacy: 78.6 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.74
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P431088

CATALOG NUMBER: LAMR4B112R509024DE010x1MW

Luminous Intensity Polar Plot





TEST NUMBER: P431088

CATALOG NUMBER: LAMR4B112R509024DE010x1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																										
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																																				
2	110	105	102	99	107	104	100	98	100	98	96	97	95	93	95	93	92	90																																				
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85																																				
4	101	94	89	86	99	93	89	85	91	87	84	89	86	83	87	84	82	81																																				
5	96	89	84	80	95	88	84	80	87	83	79	85	81	79	84	80	78	77																																				
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73																																				
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69																																				
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66																																				
9	82	73	68	65	81	73	68	65	72	68	64	71	67	64	70	67	64	63																																				
10	79	70	65	62	78	70	65	62	69	64	61	68	64	61	68	64	61	60																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	297172
5°	282734
10°	274421
15°	263307
20°	216618
25°	173563
30°	90539
35°	29206
40°	4963
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P431088

CATALOG NUMBER: LAMR4B112R509024DE010x1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.6	14.6
10°-20°	427.2	38.0
20°-30°	415.6	37.0
30°-40°	114.4	10.2
40°-50°	2.5	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1007.5	89.6
0°-40°	1121.9	99.8
0°-60°	1124.4	100.0
0°-90°	1124.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1124.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1845	
5°	1748	165
15°	1579	427
25°	976	416
35°	148	114
45°	0	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P431088

CATALOG NUMBER: LAMR4B112R509024DE010x1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1844.6
2.5°	1811.7
5°	1748.3
7.5°	1697.1
10°	1677.5
12.5°	1676.0
15°	1578.7
17.5°	1399.2
20°	1263.5
22.5°	1150.9
25°	976.4
27.5°	687.3
30°	486.7
32.5°	294.5
35°	148.5
37.5°	66.4
40°	23.6
42.5°	2.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)