

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431698

Luminaire Tested: **LAMR4B312R559040DE01021MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P431698
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-898-142)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B312R559040DE01021MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 55 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3877.5 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.81
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P431698

CATALOG NUMBER: LAMR4B312R559040DE01021MB

Luminous Intensity Polar Plot





TEST NUMBER: P431698

CATALOG NUMBER: LAMR4B312R559040DE01021MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	95	95	94	93	91	88	86	85	85	84	82	80	76															
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	88	86	85	85	84	82	80	76	76	76	76															
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	83	82	81	80	77	76	76	76	76	76	76															
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	80	80	78	77	76	75	74	73	72	72	72	72	72															
5	96	89	83	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76	76	74	73	72	71	70	70	70	70	70	70	70															
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72	72	70	69	68	67	66	66	66	66	66	66	66															
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	68	68	66	65	64	63	63	63	63	63	63	63	63															
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	72	69	66	65	65	63	62	61	60	60	60	60	60	60	60	60															
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62	62	60	59	58	57	57	57	57	57	57	57	57															
10	78	69	64	60	77	69	64	60	68	63	60	67	63	60	66	63	60	59	59	57	56	55	54	54	54	54	54	54	54	54															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2609731
5°	2646246
10°	2708155
15°	2594936
20°	2357656
25°	1894674
30°	1090701
35°	316511
40°	48369
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P431698

CATALOG NUMBER: LAMR4B312R559040DE01021MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	512.4	13.2
10°-20°	1413.5	36.5
20°-30°	1525.6	39.3
30°-40°	417.3	10.8
40°-50°	8.8	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3451.5	89.0
0°-40°	3868.8	99.8
0°-60°	3877.5	100.0
0°-90°	3877.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3877.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5290	
5°	5343	512
15°	5080	1413
25°	3480	1526
35°	526	417
45°	0	9
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P431698

CATALOG NUMBER: LAMR4B312R559040DE01021MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	5289.5
2.5°	5268.0
5°	5343.1
7.5°	5402.1
10°	5405.6
12.5°	5268.0
15°	5080.3
17.5°	4831.8
20°	4490.4
22.5°	4050.7
25°	3480.4
27.5°	2752.9
30°	1914.5
32.5°	1049.3
35°	525.5
37.5°	225.2
40°	75.1
42.5°	10.7
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)