

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P430924

Luminaire Tested: **LAMR4B112R159030DE010x1MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P430924
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-6)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B112R159030DE010x1MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 15 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1179.0 lumens
Efficiency: N/A
Efficacy: 82.4 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P430924

CATALOG NUMBER: LAMR4B112R159030DE010x1MB

Luminous Intensity Polar Plot





TEST NUMBER: P430924

CATALOG NUMBER: LAMR4B112R159030DE010x1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																																				
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96																																				
3	110	106	103	101	108	105	102	100	103	100	98	100	99	97	98	97	96	94																																				
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93																																				
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	95	94	92	91																																				
6	103	98	95	92	102	98	94	92	96	94	92	95	93	91	94	92	91	90																																				
7	101	96	93	90	100	96	92	90	95	92	90	94	91	89	93	91	89	88																																				
8	99	94	91	89	99	94	91	89	93	90	88	92	90	88	91	89	88	87																																				
9	98	92	89	87	97	92	89	87	91	89	87	91	88	87	90	88	86	86																																				
10	96	91	88	86	95	91	88	86	90	87	85	89	87	85	89	87	85	84																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1686483
5°	1423339
10°	653898
15°	203897
20°	83081
25°	27250
30°	8446
35°	1790
40°	442
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P430924

CATALOG NUMBER: LAMR4B112R159030DE010x1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	679.2	57.6
10°-20°	404.8	34.3
20°-30°	85.8	7.3
30°-40°	9.0	0.8
40°-50°	0.3	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1169.7	99.2
0°-40°	1178.7	100.0
0°-60°	1179.0	100.0
0°-90°	1179.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1179.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10468	
5°	8801	679
15°	1222	405
25°	153	86
35°	9	9
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P430924

CATALOG NUMBER: LAMR4B112R159030DE010x1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	10468.3
2.5°	10137.6
5°	8801.3
7.5°	6515.5
10°	3997.2
12.5°	2133.0
15°	1222.5
17.5°	767.8
20°	484.6
22.5°	285.9
25°	153.3
27.5°	86.6
30°	45.4
32.5°	23.0
35°	9.1
37.5°	4.8
40°	2.1
42.5°	0.5
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)