

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P430952

Luminaire Tested: **LAMR4B112R209035DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P430952
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-3)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B112R209035DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 20 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1284.8 lumens
Efficiency: N/A
Efficacy: 89.8 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.33
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P430952
CATALOG NUMBER: LAMR4B112R209035DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P430952

CATALOG NUMBER: LAMR4B112R209035DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	97				97															
2	112	108	105	103	110	106	104	102	103	101	100	101	99	97	98	97	95				94																
3	108	104	100	98	107	103	100	97	100	98	95	98	96	94	96	94	93				91																
4	105	100	97	94	104	99	96	93	97	94	92	95	93	91	94	92	90				89																
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88				87																
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86				85																
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84				83																
8	96	90	86	83	95	89	86	83	88	85	83	87	85	82	87	84	82				81																
9	94	88	84	81	93	87	84	81	86	83	81	86	83	81	85	82	81				80																
10	92	86	82	80	91	85	82	80	85	82	79	84	81	79	83	81	79				78																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4438097
5°	3751329
10°	2203407
15°	788957
20°	261052
25°	103923
30°	49678
35°	28369
40°	20481
45°	17234
50°	19880
55°	16257
60°	8091
65°	6888
70°	8511
75°	8959
80°	6819
85°	6793



TEST NUMBER: P430952

CATALOG NUMBER: LAMR4B112R209035DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	620.2	48.3
10°-20°	483.7	37.6
20°-30°	100.4	7.8
30°-40°	31.6	2.5
40°-50°	20.3	1.6
50°-60°	16.3	1.3
60°-70°	6.4	0.5
70°-80°	4.8	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1204.3	93.7
0°-40°	1235.9	96.2
0°-60°	1272.6	99.0
0°-90°	1284.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1284.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8995	
5°	7574	620
15°	1545	484
25°	191	100
35°	47	32
45°	25	20
55°	19	16
65°	6	6
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P430952

CATALOG NUMBER: LAMR4B112R209035DE010x1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	8995.3
2.5°	8665.4
5°	7574.4
7.5°	6068.7
10°	4398.1
12.5°	2774.6
15°	1544.6
17.5°	849.5
20°	497.2
22.5°	304.0
25°	190.9
27.5°	126.1
30°	87.2
32.5°	61.3
35°	47.1
37.5°	37.7
40°	31.8
42.5°	27.1
45°	24.7
47.5°	24.7
50°	25.9
52.5°	24.7
55°	18.9
57.5°	13.0
60°	8.2
62.5°	7.1
65°	5.9
67.5°	5.9
70°	5.9
72.5°	5.9
75°	4.7
77.5°	3.5
80°	2.4
82.5°	1.2
85°	1.2
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)