

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431143

Luminaire Tested: **LAMR4B112R609035DE010x1MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P431143
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B112R609035DE010x1MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1209.1 lumens
Efficiency: N/A
Efficacy: 84.6 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P431143
CATALOG NUMBER: LAMR4B112R609035DE010x1MB

Luminous Intensity Polar Plot





TEST NUMBER: P431143

CATALOG NUMBER: LAMR4B112R609035DE010x1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82			
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77			
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	69	67			
7	84	75	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63			
8	80	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	60	59			
9	77	67	62	58	76	67	61	58	66	61	57	65	60	57	64	60	57	56			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	685551
5°	662564
10°	656398
15°	640115
20°	590726
25°	529032
30°	409333
35°	245259
40°	94226
45°	34469
50°	1382
55°	1032
60°	1184
65°	700
70°	866
75°	1144
80°	1705
85°	0



TEST NUMBER: P431143

CATALOG NUMBER: LAMR4B112R609035DE010x1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.0	10.5
10°-20°	348.6	28.8
20°-30°	434.9	36.0
30°-40°	253.4	21.0
40°-50°	42.3	3.5
50°-60°	1.1	0.1
60°-70°	0.8	0.1
70°-80°	0.6	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	910.6	75.3
0°-40°	1164.0	96.3
0°-60°	1207.4	99.9
0°-90°	1209.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1209.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1390	
5°	1338	127
15°	1253	349
25°	972	435
35°	407	253
45°	49	42
55°	1	1
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P431143

CATALOG NUMBER: LAMR4B112R609035DE010x1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1389.5
2.5°	1366.6
5°	1337.8
7.5°	1321.4
10°	1310.2
12.5°	1292.0
15°	1253.2
17.5°	1195.0
20°	1125.1
22.5°	1054.0
25°	971.8
27.5°	857.8
30°	718.5
32.5°	562.9
35°	407.2
37.5°	256.8
40°	146.3
42.5°	85.8
45°	49.4
47.5°	17.0
50°	1.8
52.5°	1.2
55°	1.2
57.5°	1.2
60°	1.2
62.5°	1.2
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)