

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P430408

Luminaire Tested: **LAM4B312R259727DE01021MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P430408
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-5)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B312R259727DE01021MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 25 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3268.6 lumens
Efficiency: N/A
Efficacy: 79.9 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P430408

CATALOG NUMBER: LAM4B312R259727DE01021MB

Luminous Intensity Polar Plot





TEST NUMBER: P430408

CATALOG NUMBER: LAM4B312R259727DE01021MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97				97															
2	112	109	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	95				95															
3	109	104	101	99	107	103	100	98	101	98	96	99	96	95	96	95	93	92				92															
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	94	93	91	90				90															
5	103	98	94	91	102	97	93	91	95	92	90	94	91	89	92	90	89	88				88															
6	100	95	91	88	99	94	91	88	93	90	87	92	89	87	91	88	86	85				85															
7	98	92	88	86	97	92	88	86	91	87	85	90	87	85	89	86	84	83				83															
8	96	90	86	83	95	89	86	83	88	85	83	88	85	83	87	84	82	81				81															
9	94	88	84	81	93	87	84	81	86	83	81	86	83	81	85	82	81	80				80															
10	91	85	82	79	91	85	82	79	84	81	79	84	81	79	83	81	79	78				78															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2572473
5°	2398732
10°	1899433
15°	955939
20°	306746
25°	107277
30°	35940
35°	7218
40°	2376
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P430408

CATALOG NUMBER: LAM4B312R259727DE01021MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1313.2	40.2
10°-20°	1592.8	48.7
20°-30°	324.1	9.9
30°-40°	36.7	1.1
40°-50°	1.8	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3230.1	98.8
0°-40°	3266.8	99.9
0°-60°	3268.6	100.0
0°-90°	3268.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3268.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15968	
5°	14833	###
15°	5732	1593
25°	604	324
35°	37	37
45°	0	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P430408

CATALOG NUMBER: LAM4B312R259727DE01021MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	15967.8
2.5°	15659.0
5°	14832.7
7.5°	13469.3
10°	11611.0
12.5°	8949.0
15°	5731.5
17.5°	3228.8
20°	1789.2
22.5°	1019.4
25°	603.5
27.5°	360.9
30°	193.2
32.5°	84.6
35°	36.7
37.5°	22.6
40°	11.3
42.5°	4.2
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)